



ROEBUCK MOUNTED POINT A1 MEDIUM

Size indicates diameter x length Medium grade

Depth, external	232 "
Diameter, disc	23 mm
Diameter, external	23 mm
Diameter, shank	6.35 mm
Grade	Medium
Length	65 mm
RoHS Compliant	NA
Shape	A1
Size	2/8 x 2-1/2
Size	2/8 x 2-1/2 "
Size	23 x 65 mm
Speed, rotational max	19800