



CUSTOMER DRAWING

SECTION A-A* NOTE *

1. APPLICABLE CONTACT P/N : 175087 , 175090.
2. APPLICABLE HSG P/N : 176143 , 176146.

GREY	85024-1
COLOR	PART NO.

GENERAL TOLERANCES

10 MAX	±0.2
10 OVER 30 MAX	±0.25
30 OVER 100 MAX	±0.3
ANGLES	±5°

© 19 AMP MFG KOREA

ALL RIGHT RESERVED AMP PRODUCTS COVERED BY PATENTS
AND OR PATENTS PENDING**AMP** * AMP MFG KOREAWIRE RANGE
0.3-1.25 mm²INSULATION DIA
1.6 - 2.9mmNAME
**RUBBER PLUG FOR 187 SEALED
CONNECTOR**MATERIAL
NBRFINISH/COLOR
SEE TABLETOLERANCES
0 < X < 10 ±0.2
10 ≤ X < 30 ±0.25
30 ≤ X < 100 ±0.3
ANGLES 3SIZE
A3LOC
DS

NO

85024SCALE
10/1REV
0SHEET
1/1

RELEASED(P93-042)	JK	CS	4/19/83
LTR	REVISION RECORD	DR	CHK DATE

DR
EH HONGAPP
CS LEECHK
JK SONGREL
JK SONGPRINT DIST.
DO NOT SCALE PRINT