


Models 72915 2mm Sheathed Jack to 2mm Unsheathed Plug Adapter



Features

- 2mm sheathed jack to 2mm unsheathed plug adapter.
- Accepts 2mm safety-sheathed banana plugs

Materials

- Insulation: Polyamide
- Plug body: Nickel plated Brass
- Contact Spring: Nickel plated Beryllium copper.
-

Ordering Information

Model: 72915-Color Sold in packages of 10 pieces
Available colors: Black (-0) or Red (-2)

Specifications

Max Current	Max. 10A
Max Voltage	33 V AC / 70 V DC
Temperature	-20° C + 80° C
Max Resistance	Less than 0 .8 mΩ

Rating: *hands free testing* in controlled environment:
70Vrms max. For CE compliance: Not intended for hand-held use at voltages above 33Vrms/70Vdc

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 International: 425-446-5500

e-mail: technicalsupport@pomonatest.com

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.