



PART NAME			NBF SERIES PLASTIC NEMA BOX			PART No.		NBF-32022 & NBF-32122 & NBF-32222 & NBF-32322 & NBF-32422			REVISION DATE		8/12/2010	
MATERIAL		FLAMMABILITY RATING		CONTINUOUS OPERATING TEMP.		FINISH: BODY_____ LIGHT GRAY COVER_____ LIGHT GRAY OR CLEAR LATCHES & HINGES_____ PLASTIC WALL MOUNTING BRACKETS__ STAINLESS STEEL & HARDWARE								
ABS		UL94-HB		-40°C ~ +60°C / -40°F ~ 140°F		COVER 13.780in [350.00mm] C </								




ϕ .157in [4.00mm]
FOR M5 x 10mm LG. SELF-TAPPING SCREWS (ABS VERSIONS ONLY)
M5 THREADED INSERTS ON ALL OTHER VERSIONS
USE M5 x 8mm LG. MACHINE SCREWS.

ϕ .157in [4.00mm]
FOR M5 x 10mm LG. SELF-TAPPING SCREWS 4 PLCS.



ASSEMBLY



- NOTES:**
- 1) UNIT COMES COMPLETE WITH (4) WALL MOUNTING BRACKETS & (4) M5 x 10mm LG. SELF-TAPPING SCREWS. (NOT SHOWN)
 - 2) BOXES DESIGNED TO MEET FOLLOWING STANDARDS: NEMA 1,2,4,4X, AND IEC529-IP65 REQUIREMENTS.
- TOLERANCE:**
- ALL DIMENSIONS HAVE ± 0.039 in [± 1 mm]
TOLERANCE UNLESS OTHERWISE SPECIFIED.

PART NO.	MATERIAL		USE
	BODY	COVER	
NBF-32022	ABS	ABS	INDOOR
NBF-32122	ABS / PC	ABS / PC	INDOOR
NBF-32222	ABS / PC	CLEAR PC	INDOOR
NBF-32322	PBT / PC	PBT / PC	OUTDOOR
NBF-32422	PBT / PC	CLEAR PC	OUTDOOR

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[NBF32022](#) [NBF-32222](#) [NBF-32422](#) [NBF-32322](#) [NBF-32022](#) [NBF-32122](#)