

SPECIFICATION SHEET
JFW MODEL A-211-XXX-125
HYBRID ATTENUATOR

JFW Industries, Inc.
Phone: 317-887-1340
sales@jfwindustries.com
www.jfwindustries.com

Frequency Range	DC-3000 MHz
Attenuation Values	1 through 20 dB in any 1 dB increment
VSWR	1.15:1 maximum DC-1000 MHz 1.2:1 maximum 1000-2000 MHz 1.25:1 maximum 2000-3000 MHz
Attenuation Accuracy	DC-1000 MHz ± 0.3 dB (1-10 dB) ± 0.4 dB (11-20 dB) 1000-2000 MHz ± 0.4 dB (1-10 dB) ± 0.6 dB (11-20 dB) 2000-3000 MHz ± 0.6 dB (1-10 dB) ± 0.75 dB (11-20 dB)
RF Input Power	125 Watts average 1000 Watts peak
Physical Size	See outline drawing 592-075

ECR/ECN #	DATE	REV	APPR / DATE	ECR/ECN #	DATE	REV	APPR / DATE
	01/18/1995						
9999	09/04/2003	A	SL 04/21/2004				