




Top View of Assembly




SECTION A-A End View of Assembly




1555U



SECTION B-B Side View of Assembly





Top View Looking Inside Box




Available 16 Gauge Steel
Plate

Maximum P.C. Board Size

NOTE: Hole patterns same
as seen in top view of box.



Lid



NOTE
Purchased assembly includes box, lid and 4 cover screws.
Cover screws should be torqued to 2.5 lbf-in (30 cN-m)
Polycarbonate version is 508 approved
Enclosure Type 4X, 4, 12 File# E65324

1555U	
1555U Regular Enclosure	
General Purpose ABS	1555UGY
Polycarbonate	1555U2GY
ACCESSORIES	
Heavy Duty 16 Gauge Galvanized Steel Panels	1554UPL
Steel Panel / P.C. Board Machine Screw [M3 X 8mm Nickel Plated]	1591MM100
Steel Panel / P.C. Board Self Tapping Screw [#6 X 1/4" (6.4mm) Nickel Plated]	1598ATS100
Cover Screws (Pkg 4)	SC1554
[M4 X 20mm Stainless Steel]	

