





TERMINAL DETAIL
SCALE 2X

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 4A @125VAC, 2A @250VAC
5. CONTACT RESISTANCE: 10mILLI-OHMS
6. DIELECTRIC STRENGTH: 1500 VAC-1Minute
7. MATERIALS:


HOUSING: ZINC ALLOY DIE CAST
CYLINDER: ZINC ALLOY W/CHROME PLATING
TERMINAL AND CONTACTS: SILVER PLATING
KEYS 125 (2): BRASS W/NICKEL PLATING
DOUBLE CUT REVERSIBLE



CIRCUIT: SPDT
CONTACT CONFIGURATION

SWITCH FUNCTION	
A	B
↕	→
DN	DN

- LEGEND
- = OFF POSITION
 - = INDICATES KEY PULL
 - ⊗ = INDICATES NO KEY PULL



RECOMMENDED PANEL CUTOUT

KEYS 125 (2): BRASS W/NICKEL PLATING DOUBLE CUT REVERSIBLE					E-SWITCH®				
					TITLE K0118A-125				
A	11376	RELEASED FOR PRODUCTION	4/4/01	CJB	SCALE 1.5:1	DATE 4/4/01	DR CJB	DWG K200117	REV A
REV.	ECN No.	DESCRIPTION	DATE	CHKD					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED									

E-SWITCH®

K01184-125