



Clamps and Shields (Hoods)



A




B



C



D



E

Straight/90° Exit Cable Clamps (Hoods)

Assemblies can be used on either plugs or receptacles and will not interfere with commonly used hardware.

Black Thermoplastic

Finish is textured. Black zinc-plated steel flat head screws.

Stock No.	Mfr.'s Type	Fig.	Case Style	EACH		
				1-24	25-99	100-499
512-0605	207467-1	A	9-Pin	1.95	1.75	1.46
512-0610	207470-1	A	15-Pin	2.40	2.16	1.80
512-0615	207345-1	A	25-Pin	2.46	2.21	1.84
512-0620	207473-1	A	37-Pin	2.52	2.26	1.89
512-0625	207476-1	A	50-Pin	2.49	2.24	1.87

Grey Thermoplastic

4-40 zinc-plated steel screws.

512-0705	206471-1	B	15-Pin	2.60	2.10	1.89
512-0710	206472-1	B	25-Pin*	2.61	2.35	1.96
512-0715	745134-1	B	25-Pin**	2.61	2.35	1.96
512-0720	745081-1	B	37-Pin	2.65	2.39	1.99
512-0725	745082-1	B	50-Pin	3.45	3.13	2.87

*Cable dia. 0.335". **Cable dia. 0.460".

Straight Exit Dataphone Cable Clamps (Hoods)

512-1000	745122-2	C	15-Pin	8.88	8.00	7.26
512-1005	745121-2	C	25-Pin	6.39	5.75	4.79

2-Piece 90° Exit RFI/EMI Shields (Die Cast)

Stock No.	Mfr.'s Type	Fig.	Max. Cable Dia.	Case Style	EACH		
					1-24	25-99	100-499
512-0950	745652-2	D	0.375	15-Pin	9.70	8.73	7.28
512-0955	745653-4	D	0.350	25-Pin	14.71	13.24	11.03
512-0960	745653-3	D	0.430	25-Pin	11.47	10.32	8.60

2-Piece Straight Exit RFI/EMI Shields

Die Cast Metal

Zinc alloy plated bright nickel over bright copper.

Stock No.	Mfr.'s Type	Fig.	Max. Cable Dia.	Case Style	EACH		
					1-24	25-99	100-499
512-0803	745171-2	F	0.200	9-Pin	4.94	4.45	3.71
512-0805	745171-1	F	0.250	9-Pin	4.33	3.90	3.25
512-0810	745172-2	F	0.300	15-Pin	5.62	5.06	4.22
512-0812	745172-1	F	0.375	15-Pin	4.81	4.32	3.60
512-0814	745173-5	F	0.280	25-Pin	5.89	5.30	4.42
512-0815	745173-4	F	0.350	25-Pin	4.58	4.12	3.43
512-0820	745173-3	F	0.430	25-Pin	4.58	4.12	3.43
512-0822	745173-2	F	0.480	25-Pin	6.03	5.43	4.52
512-0825	745174-4	F	0.425	37-Pin	6.28	5.65	4.71
512-0830	745174-3	F	0.500	37-Pin	6.17	5.55	4.62
512-0835	745175-5	F	0.450	50-Pin	6.46	5.81	4.85
512-0838	745175-4	F	0.525	50-Pin	6.39	5.75	4.79

Metal-Plated Plastic

Plated nickel over copper.



512-0903	745854-5	F	0.200	9-Pin	3.20	2.89	2.40
512-0905	745854-3	F	0.250	9-Pin	2.88	2.59	2.16
512-0908	747099-5	F	0.300	15-Pin	5.10	4.59	3.83
512-0910	747099-3	F	0.375	15-Pin	3.11	2.79	2.33
512-0912	745833-9	F	0.280	25-Pin	2.88	2.59	2.16
512-0915	745833-7	F	0.350	25-Pin	3.33	3.00	2.50
512-0920	745833-5	F	0.430	25-Pin	5.26	4.73	3.94
512-0922	745833-3	F	0.480	25-Pin	8.86	7.98	6.65
512-0930	747100-5	F	0.500	37-Pin	7.46	6.71	5.59

Clamp Shell Straight/45° Exit Hoods

Assemblies can be used on either plug or receptacle and will not interfere with commonly used hardware. Black thermoplastic, textured finish, zinc-plated steel pan head screws. (6-32). 1.625" length short cable clamp.

Stock No.	Mfr.'s Type	Pins	EACH		
			1-24	25-99	100-499
512-0505	205729-1	9	1.80	1.62	1.35
512-0509†	206393-1	15	2.72	2.45	2.04
512-0510	205730-1	15	2.15	1.94	1.61
512-0513†	206390-1	25	3.45	3.10	2.58
512-0515	205718-1	25	1.65	1.48	1.24
512-0520	205731-1	37	2.24	2.00	1.67
512-0525	205732-1	50	2.52	2.26	1.89

†1.25" length short cable clamp.



Quik-Snap Backshell Kits Straight/60° Exit

Designed for ease of assembly. Assemblies can be used with plugs or receptacles and will not interfere with commonly used hardware. Black polypropylene.

Stock No.	Mfr.'s Type	Case Style	EACH		
			1-24	25-99	100-499
512-0850	749914-2	9-Pin	1.34	1.20	1.00
512-0852	749915-2	15-Pin	1.34	1.20	1.00
512-0854	749626-2	25-Pin	1.34	1.20	1.00
512-0856	749916-2	37-Pin	1.54	1.39	1.16

Male Screw Retainers



Kit contains 2 male-screws and 2 clips. Screws are made of zinc-plated steel with a yellow or clear chromate finish. Retaining clips are made of zinc-plated steel. Type 205980-1 for metal shell connectors. Type 745647-1 for all plastic connectors. All parts packaged unassembled. Thread size 4-40.

Stock No.	Mfr.'s Type	Description	Screw Length	PER SET/2		
				1-99	100-499	500-999
512-9050	205980-1	Yellow chromate finish	.220"	.42	.38	.31
512-9052	205980-4	Clear chromate finish	.220"	.51	.46	.38
512-9055	745647-1	For all plastic D-sub	.220"	.49	.44	.37

Locking Posts



Kit contains 2 complete post assemblies. Constructed of cold-rolled zinc plated steel. 4-40 threaded. Size: .416" long. 512-9080. Type 206514-1. 1-99.....PER SET/2 1.80 100-499.....PER SET/2 1.62 500-999.....PER SET/2 1.35

Female Screw Locks

Female screw locks for use with either metal or plastic connector shells. Available in square or hex nut types; short, standard, or long sizes. Each kit contains two female screw lock assemblies. All parts packaged unassembled. Includes female screw lock screw, two flat washers, lockwasher, and hex or square nuts (except 748270-2).

Stock No.	Mfr.'s Type	Nominal Type	Finish	Size Nut	Nut Type	Screw Length	PER SET/2		
							1-99	100-499	500-999
512-9060	207952-1	Short	Yellow chromate	0.250	Square	0.250	1.11	1.00	.83
512-9065	207952-3	Short	Clear chromate	0.250	Square	0.250	1.27	1.14	.95
512-8739	745563-1	Short	Yellow chromate	0.250	Hex	0.250	1.35	1.21	1.01
512-8758	745563-3	Short	Clear chromate	0.250	Hex	0.250	1.20	1.08	.90
512-9070	205817-1	Standard	Yellow chromate	0.350	Hex	0.312	.99	.89	.74
512-9072	205817-3	Standard	Clear chromate	0.350	Hex	0.312	.99	.89	.74
512-0559	748270-2*	Standard	Clear chromate	0.350	Hex	0.312	.69	.62	.52
512-9075	207719-1	Long	Yellow chromate	0.350	Hex	0.560	1.20	1.08	.90
512-9077	207719-3	Long	Clear chromate	0.350	Hex	0.560	1.14	1.02	.85

*Not a set of 2.

