

Digital DC Power Supply with RS-232 Interface

Regulated 30V/3A DC Supply with 9 user-programmable output memories, remote PC control

Features:

- Two large 3-1/2 Digit LED displays for Ammeter and Voltmeter
- Constant Voltage and Current with high load/line regulation and low noise/ripple
- Digital keypad operation for easy programming and setup
- Instant recall of output presets at the touch of a key
- 9-step memory for programmed (manual or timed) outputs and test routines
- Galvanized steel case with binding post connectors
- Built-in RS-232 bi-directional PC interface
- Complete with power cable, PC Windows™ software disk, and RS-232 interface cable.



CE

Specifications:		
DC Output Supply:	Voltage	0 - 30 VDC
	Current	0 - 3A DC
Ripple and Noise (RMS):	<1mV	
Line and Load Regulation:	<0.02% + 5mV	
Power:	110/220VAC 50/60Hz	
Dimensions/Weight:	8 x 4.5 x 10.6" (205 x 115 x 270mm) / 14.7 lbs (6.7 kg)	

Ordering Information:

382207Digital DC Power Supply with RS-232 Interface

EXTECH INSTRUMENTS CORPORATION
285 Bear Hill Road, Waltham, MA 02451-1064, U.S.A.
Phone: 781-890-7440 • FAX 781-890-7864

ISO 9001:2000 CERTIFIED

Make mine an Extech!
www.extech.com



08/03 - R1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[382207](#)