



4		3		2		1											
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION													
© COPYRIGHT - By -				ALL RIGHTS RESERVED.													
LOC G		DIST 86		REVISIONS													
P		LTR		DESCRIPTION		DATE	DWN	APVD									
		E2		REVISED PER ECO-11-005027		11MAR11	RK	HMR									
AMP WIRE RANGE		FILE E66717		LR7189 Certified													
12-10 AWG STRANDED		12-10 AWG STRANDED		12-10 AWG STRANDED													
																	
				1 MARKED AMP 12-10 2 DESIGNED FOR WIRE INSULATION DIA OF .135-.210. 3 MATES WITH .250±.003 BY .032±.001 THK TAB. 4 BODY: BRASS, TIN PLATED SLEEVE: NYLON, YELLOW 5 RATED FOR 24 MAX AMPERE													
				<table><tr><td>100</td><td>LOOSE PIECE</td><td>8-696371-1</td></tr><tr><td>1000</td><td>LOOSE PIECE</td><td>696371-1</td></tr><tr><td>QTY</td><td>PACKAGE TYPE</td><td>PART NO.</td></tr></table>					100	LOOSE PIECE	8-696371-1	1000	LOOSE PIECE	696371-1	QTY	PACKAGE TYPE	PART NO.
100	LOOSE PIECE	8-696371-1															
1000	LOOSE PIECE	696371-1															
QTY	PACKAGE TYPE	PART NO.															
TE CONNECTIVITY CUSTOMER SERVICE SYSTEM		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F] -		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 07NOV01											
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWING AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: INCHES		CHK T MICHELUTTI 07NOV01											
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± - FINISH		APVD T MICHELUTTI 07NOV01											
FOR ORDER ENTRY		1-800-526-5142		CIRCULAR MIL AREA: 5,180-13,100 STRANDED		NAME RECEPTACLE, 250 SERIES, FASTON, FULLY INSULATED, WIRE: 12-10 AWG											
				MATERIAL - 4		PRODUCT SPEC - APPLICATION SPEC 114-13076											
						WEIGHT -											
						CUSTOMER DRAWING											
						SCALE 1:1											
						SHEET 1 OF 1											
						REV E2											