




## TM-131 防塵ゴム

### Sealing Rubber Gasket



#### 特長

サイズ違いが豊富な防塵ゴムです。

#### 用途

計装・制御盤・工作機械・家電・医療機器・家具・事務機器等

#### 仕様

連続気泡につき防水には対応しておりません。場合によっては継目が入り、段差ができることがあります。

#### 材質と処理 Material & Finish

| 材質 Material            | 処理 Finish |
|------------------------|-----------|
| ラテックススポンジ Latex Sponge | 黒色 Black  |

#### ■ L 寸法許容差 L dimensional Tolerance

| 寸法範囲<br>size                 | 100 以下<br>(100 or less) | 100 を超え 200 以下<br>(Over 100, 200 or less) | 200 を超え 500 以下<br>(Over 200, 500 or less) |
|------------------------------|-------------------------|-------------------------------------------|-------------------------------------------|
| 許容差<br>Dimensional Tolerance | +5                      | +10                                       | +25                                       |

※ 500 を超える寸法は L 寸法の +5% です。  
Size over 500 will be +5% of L dimension.

#### Characteristic

Many types are available to meet various types of application.


#### Application

Instruments / Control boards / Machine tools / Home appliances / Medical instruments / Furniture / Office utilities, etc.

#### Specification

No waterproof ability because it is made by continuous foaming.  
Please be aware that there may be joints and steps on the product.

L=ご希望の長さに切断いたします。(テープはB寸法の面に付いています。)  
L: Please specify when ordering. (Tape shall be set on the B-surface.)



●納期についてはご相談ください。  
Please contact us for the lead time.

#### 寸法・仕様表 Size List & Specification テープ付 With Tape

※テープ付きは品番の後に T がつきます。  
Model no. with T on this list means gasket with tape.

#### 寸法・仕様表 Size List & Specification テープなし Without Tape

| 型番 Model No. | A  | B  | 価格(円 /1m) Price (yen) |
|--------------|----|----|-----------------------|
| TM-131-1     | 3  | 12 | ¥240                  |
| TM-131-2     |    | 15 | ¥260                  |
| TM-131-3     |    | 20 | ¥260                  |
| TM-131-4     |    | 25 | ¥290                  |
| TM-131-5     |    | 30 | ¥310                  |
| TM-131-7     | 5  | 10 | ¥260                  |
| TM-131-8     |    | 15 | ¥260                  |
| TM-131-9     |    | 20 | ¥290                  |
| TM-131-10    |    | 30 | ¥365                  |
| TM-131-11    | 7  | 40 | ¥495                  |
| TM-131-13    |    | 15 | ¥290                  |
| TM-131-14    |    | 20 | ¥335                  |
| TM-131-15    |    | 30 | ¥475                  |
| TM-131-16    | 8  | 8  | ¥260                  |
| TM-131-17    |    | 10 | ¥275                  |
| TM-131-18    |    | 12 | ¥290                  |
| TM-131-19    | 10 | 12 | ¥310                  |
| TM-131-20    |    | 15 | ¥365                  |
| TM-131-21    |    | 20 | ¥505                  |
| TM-131-22    |    | 25 | ¥600                  |
| TM-131-23    |    | 30 | ¥695                  |
| TM-131-24    |    | 35 | ¥805                  |
| TM-131-25    |    | 40 | ¥925                  |
| TM-131-26    | 12 | 12 | ¥370                  |
| TM-131-27    |    | 15 | ¥435                  |
| TM-131-28    |    | 20 | ¥565                  |
| TM-131-32    | 15 | 15 | ¥550                  |
| TM-131-33    |    | 20 | ¥695                  |
| TM-131-34    |    | 25 | ¥875                  |
| TM-131-35    |    | 30 | ¥1,045                |
| TM-131-37    | 20 | 20 | ¥925                  |
| TM-131-38    |    | 25 | ¥1,155                |
| TM-131-39    |    | 30 | ¥1,390                |
| TM-131-41    |    | 40 | ¥1,850                |

| 型番 Model No. | A  | B  | 価格(円 /1m) Price (yen) |
|--------------|----|----|-----------------------|
| TM-131-1T    | 3  | 12 | ¥390                  |
| TM-131-2T    |    | 15 | ¥390                  |
| TM-131-3T    |    | 20 | ¥390                  |
| TM-131-4T    |    | 25 | ¥390                  |
| TM-131-5T    |    | 30 | ¥410                  |
| TM-131-7T    | 5  | 10 | ¥400                  |
| TM-131-8T    |    | 15 | ¥400                  |
| TM-131-9T    |    | 20 | ¥430                  |
| TM-131-10T   |    | 30 | ¥530                  |
| TM-131-11T   | 7  | 40 | ¥680                  |
| TM-131-13T   |    | 15 | ¥430                  |
| TM-131-14T   |    | 20 | ¥490                  |
| TM-131-15T   |    | 30 | ¥680                  |
| TM-131-16T   | 8  | 8  | ¥390                  |
| TM-131-17T   |    | 10 | ¥410                  |
| TM-131-18T   |    | 12 | ¥425                  |
| TM-131-19T   | 10 | 12 | ¥450                  |
| TM-131-20T   |    | 15 | ¥525                  |
| TM-131-21T   |    | 20 | ¥680                  |
| TM-131-22T   |    | 25 | ¥780                  |
| TM-131-23T   |    | 30 | ¥855                  |
| TM-131-24T   |    | 35 | ¥990                  |
| TM-131-25T   |    | 40 | ¥1,140                |
| TM-131-26T   | 12 | 12 | ¥525                  |
| TM-131-27T   |    | 15 | ¥600                  |
| TM-131-28T   |    | 20 | ¥750                  |
| TM-131-32T   | 15 | 15 | ¥705                  |
| TM-131-33T   |    | 20 | ¥860                  |
| TM-131-34T   |    | 25 | ¥1,070                |
| TM-131-35T   |    | 30 | ¥1,290                |
| TM-131-37T   | 20 | 20 | ¥1,120                |
| TM-131-38T   |    | 25 | ¥1,420                |
| TM-131-39T   |    | 30 | ¥1,710                |
| TM-131-41T   |    | 40 | ¥2,285                |

特注品のご相談承ります Please contact us for custom-made.