

MICRO SWITCHA DIVISION OF MILWAUKEE-HONEYWELL REGULATOR COMPANY
PROSPERITY, ILLINOIS

FED. MFR. CODE 91929

SWITCH—BASIC

CATALOG LISTING

4BS3**4BS3****M**DRAWING
NUMBER

ISSUE

8

REPLACES

RELEASE NO. SR 4441

CWT 1 JUNE 63

CHECK

REH 1 JUNE 63

CHECK

REH 1 JUNE 63

CHECK

REH 1 JUNE 63

CHECK

REH 1 JUNE 63

CHECK

REH 1 JUNE 63

CHECK


REH 1 JUNE 63

CHECK

REH 1 JUNE 63

CHECK

REH 1 JUNE 63

**NOTE -**

- 1-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX. DIA. ON 1.000 ± .002 CENTERS.
- 2-SWITCH IS CAPABLE OF BEING SUBMERGED IN 2 INCHES OF WATER FOR ONE HOUR WITHOUT DETERIORATION OF SEALANT AND WITHOUT INDICATION OF LEAKAGE
- 3-SWITCH WILL WITHSTAND 3 P.S.I. HYDROSTATIC PRESSURE FOR 3 MINUTES MIN.
- 4 A BAND OF EPOXY .010 MAX THICK X .125 MAX WIDE IS PERMITTED AT THE JUNCTION OF THE COVER AND CASE

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — — 40 GRAMS MAX.

RELEASE FORCE — — — 20 GRAMS MIN.

"G" LOAD — — — 5-8 "G"

ELECTRICAL DATACONTACT ARRANGEMENT
S. P. N. C.

B

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT .050 LB.