


Part Number: 67673-1001
0.80mm Pitch I/O Receptacle, Surface Mount, Right Angle, 14 Circuits, Lead-Free
Image not available

Status: Planned for Obsolescence
Series: 67673
Category: I/O Connectors

Series image - Reference only
Mates With Part(s):
[67674](#)
Product Environmental Compliance
EU RoHS: ELV and RoHS Compliant

China RoHS:
REACH SVHC:
Low-Halogen Status: Not Reviewed

Part Detail
General

Status	Planned for Obsolescence
Category	I/O Connectors
Series	67673
Application	Wire-to-Board
Component Type	Receptacle
Product Name	N/A
Type	N/A

Physical

Circuits (Loaded)	14
Circuits (maximum)	14
Lock to Mating Part	None
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Panel Mount	No
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.254µm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Surface Mount

Electrical
(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1.5A
Shielded	Yes
Voltage - Maximum	200V

Material Info

UPC	822350624756
-----	--------------

Reference - Drawing Numbers

Product Specification	PS-67673-003
Sales Drawing	SD-67673-005
Test Summary	TS-67673-003

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application
Tooling**

[Check our list of old tooling that used to be
available for this part](#)