



3D Step-file
available on request



Further specifications and options in section „E-G“ / Weitere Spezifikationen und Optionen in Kapitel „E-G“ / Autres spécifications et options au chapitre „E-G“										
Type / Typ / Type	Body / Körper / Corps		Accessories Zubehör Accessoires	Cap / Farbkappe / Cabochon	Light source Lichtquelle Source lum.			Voltage Spannung Tension		
	Surface Oberfläche Surface	Protection Schutzart Protection						Code	V	mA
943 Screw terminals Schraubanschlüsse Contact à vis All versions also available as flashing units. Put a "F" for flashing at the end of the part#. Alle Versionen auch blinkend erhältlich. Bitte ergänzen Sie ein „F“ am Ende der Artikel#. Version clignotante possible pour tous les modèles. Ajouter la lettre "F" à la référence.	Black Schwarz Noir Material: ABS Material: ABS Matériel: ABS	IP65	Nut & O-Ring Mutter & O-Ring Ecrou & Joint 	B Blue Blau Bleu	B0 1 LED 3000mcd 470nm	Blue Blau Bleue	B 12V AC/DC	20		
				G Green Grün Vert	G0 1 LED 3000mcd 525nm	Green Grün Verte	D 24V AC/DC	20		
				R Red Rot Rouge	R0 1 LED 800mcd 660nm	Red Rot Rouge	Z 230V AC	20		
				W White Weiss Blanc	W0 1 LED 1200mcd 6500K	White Weiss Blanche				
				Y Yellow Gelb Jaune	Y0 1 LED 1200mcd 592nm	Yellow Gelb Jaune				

Operating Temperature -25° to +60°C / Storage Temperature: -25° to +60°C

RoHS compliant

Specifications are subject to change without notice – Änderungen die dem technischen Fortschritt dienen, sind vorbehalten – Réserve de modifications de toutes les données techniques