


PANDUIT PART NUMBER	COPPER CONDUCTOR SIZE	EXPANDED WIRE RANGE**	BARREL		OVERALL LENGTH "A" ± .06	WIRE STRIP LENGTH	PANDUIT CRIMP TOOL PART NUMBERS					
			CT-700 (OBSOLETE)	CT-1700			CT-720	CT-920/CT-920CH CT-930/CT-930CH CT-940CH* CT-2920 CT-2940*	CT-980 CT-980CH CT-2950 CT-2980	CT-2001		
											DIE PART NO./ DIE SET COLOR & INDEX NO./ NUMBER OF CRIMPS	
SCL8-L	#8 AWG	————	0.18	0.27	2.25	1-1/16	CD-700-8-2 RED P21 3 CRIMPS	RED P21 3 CRIMPS	CD-720-1 RED P21 2 CRIMPS	CD-920-8 RED P21 1 CRIMP	————	CD-2001-8 RED P21 2 CRIMPS
SCL6-L	#6 AWG	————	0.22	0.31	2.38	1-1/8	CD-700-8-2 BLUE P24 3 CRIMPS	BLUE P24 3 CRIMPS	CD-720-1 BLUE P24 2 CRIMPS	CD-920-6 BLUE P24 1 CRIMP	————	CD-2001-6 BLUE P24 2 CRIMPS
SCL4-L	#4 AWG, #3 AWG, #2 SOL	————	0.28	0.38	2.38	1-1/8	CD-700-8-2 GRAY P29 3 CRIMPS	GRAY P29 3 CRIMPS	CD-720-1 GRAY P29 2 CRIMPS	CD-920-4 GRAY P29 1 CRIMP	STD 1 CRIMP	CD-2001-4 GRAY P29 2 CRIMPS
SCL2-Q	#2 AWG	#6-#2 STR. AWG	0.31	0.42	2.62	1-1/4	CD-700-8-2 BROWN P33 3 CRIMPS	BROWN P33 3 CRIMPS	CD-720-1 BROWN P33 2 CRIMPS	CD-920-2 BROWN P33 1 CRIMP	STD 1 CRIMP	CD-2001-2 BROWN P33 2 CRIMPS
SCL1-E	#1 AWG	#6-#1 STR. AWG	0.36	0.47	2.87	1-3/8	CD-700-1-1/0 GREEN P37 3 CRIMPS	GREEN P37 3 CRIMPS	CD-720-2 GREEN P37 2 CRIMPS	CD-920-1 GREEN P37 1 CRIMP	STD 1 CRIMP	CD-2001-1 GREEN P37 2 CRIMPS
SCL1/0-X	1/0 AWG	#6-#1/0 STR. AWG	0.39	0.52	2.87	1-3/8	CD-700-1-1/0 PINK P42 3 CRIMPS	————	CD-720-2 PINK P42 2 CRIMPS	CD-920-1/0 PINK P42 2 CRIMPS	STD 2 CRIMPS	CD-2001-1/0 PINK P42 2 CRIMPS
SCL2/0-X	2/0 AWG	#4-#2/0 STR. AWG	0.45	0.58	3.13	1-1/2	————	————	CD-720-2 BLACK P45 3 CRIMPS	CD-920-2/0 BLACK P45 3 CRIMPS	STD 2 CRIMPS	CD-2001-2/0 BLACK P45 3 CRIMPS
SCL3/0-X	3/0 AWG	#2-#3/0 STR. AWG	0.51	0.64	3.12	1-1/2	————	————	CD-720-2 ORANGE P50 3 CRIMPS	CD-920-3/0 ORANGE P50 3 CRIMPS	STD 2 CRIMPS	CD-2001-3/0 ORANGE P50 3 CRIMPS
SCL4/0-X	4/0 AWG	#1-#4/0 STR. AWG	0.57	0.71	3.37	1-5/8	————	————	CD-720-3 PURPLE P54 3 CRIMPS	CD-920-4/0 PURPLE P54 3 CRIMPS	STD 3 CRIMPS	CD-2001-4/0 PURPLE P54 3 CRIMPS
SCL250-X	250 kcmil	#1/0-250 kcmil	0.63	0.77	3.38	1-5/8	————	————	CD-720-3 YELLOW P62 4 CRIMPS	CD-920-250 YELLOW P62 3 CRIMPS	STD 3 CRIMPS	CD-2001-250 YELLOW P62 3 CRIMPS

*CD-920 DIES CAN BE USED WITH CT-940CH AND CT-2940 TOOLS WITH CD-940-DA DIE ADAPTER.

**WITH CT-980, CT-980CH, CT-2950 & CT-2980



NOTES:
MATERIAL - HIGH CONDUCTIVITY
SEAMLESS COPPER TUBING.

ELECTRO-TIN PLATED.

BARREL COLOR CODED WITH DIE SET
INDEX NUMBER.

UL LISTED WITH CODE COPPER CONDUCTORS
FOR APPLICATIONS UP TO 35KV, FILE E52164.

CONSULT CABLE MANUFACTURER FOR VOLTAGE
STRESS RELIEF INSTRUCTIONS WITH
APPLICATIONS GREATER THAN 2000 VOLTS.

CSA CERTIFIED FOR APPLICATIONS
UP TO 600V, FILE LR31212.

FOR USE WITH COPPER CABLES ONLY.



CAD FILENAME/LAYERS							C41062_04		
							PANDUIT CORP TINLEY PARK, ILLINOIS		
							SCL LONG BARREL #8 THRU 250 COPPER SPLICES		
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
04	2-03	SAC		EXPANDED WIRE RANGE FOR SCL4-L, REMOVED NAVY NUMBERS & UPDATED SCL250-X MCM TO kcmil			09358	TRO	JAC
03	4-01	TC	SKB	ADDED: LETTER P TO DIE NO'S. & CD-920 DIE NOTE; TOOLS CT-940CH, CT-2920, CT-2940, CT-2950, CT-2980; UL & CSA LOGOS, EXPANDED WIRE RANGE; REMOVED: ALTERNATE DIE INDEX NO'S. & NOTE; FLEX & WELD CONDUCTOR SIZES; CHANGED: CRIMP QTY'S.	09358		TRO	JAC	
02	1-93	WL		REVISED NOTES/ ADDED TOLERANCES & CT-980/ CT-980CH	01369		RAK	LA	
01	12-92	WL	GRM	ADDED CT-2001	01307		RJM	RS	DRAWN BY WL
00	5-92	WL	GRM	RELEASED	00980			RS	DATE 5-12-92
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST	CHK'D GRM	MAT'L: SEE NOTES ABOVE
							SCALE N/A		DRAWING NO. C41062
									DWG SIZE B