

Pocket Foot Candle Light Meter



Measures up to 2,000Fc
For basic lighting applications

Features:

- Large 3-1/2 digit (1999 count) LCD with over-range indication
- Two ranges: 200.0 (0.1Fc) and 2000 (1Fc)
- 5% basic accuracy
- Precision color-corrected, photo-diode sensor
- Battery operated with low battery indication
- Complete with 9V battery, remote light sensor with 47" (1.2m) cable, and built-in stand

Applications:

- Workplace, clean-room, and computer room light testing
- Compliance with safety regulatory bodies (OSHA)
- Ambient testing for light-sensitive archives such as in museums and art galleries
- Schools, library and parking lot light testing
- Building and ATM area security light monitoring



Ordering Information:

401027Foot candle Light Meter
401027-NIST401027 with NIST Certificate

