


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO. SPC-F004 * Effective: 12/21/98 * DCP No: 680					
DCP #	REV	DESCRIPTION		DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
182	A	RELEASED		J.W.M.	9/24	J.C.	10/10/97	B.B.	10/10/97
1779	B	RoHS ADDED		DCM	1/24/06	JWM	1/24/06	JWM	1/24/06



SPC Type Number	Thread Size	"L"	"A"
2415	4-40	1/4 [6.35]	1/4
2416	4-40	3/8 [9.53]	1/4
2417	4-40	1/2 [12.70]	1/4
2418	4-40	5/8 [15.88]	1/4
2419	4-40	3/4 [19.05]	1/4
2420	4-40	7/8 [22.22]	1/4
2421	4-40	1 [25.40]	1/4
2422	6-32	1/4 [6.35]	1/4
2423	6-32	3/8 [9.53]	1/4
2424	6-32	1/2 [12.70]	1/4
2425	6-32	5/8 [15.88]	1/4
2426	6-32	3/4 [19.05]	1/4
2427	6-32	7/8 [22.22]	1/4
2428	6-32	1 [25.40]	1/4
2429	8-32	1/4 [6.35]	1/4
2430	8-32	3/8 [9.53]	1/4
2431	8-32	1/2 [12.70]	1/4
2432	8-32	5/8 [15.88]	1/4
2433	8-32	3/4 [19.05]	1/4
2434	8-32	7/8 [22.22]	1/4
2435	8-32	1 [25.40]	1/4

NOTE: On threaded spacers 3/4" and longer, the tap is 3/8" from each end and not continuous through.

SPC-F004.DWG

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

Unless Otherwise Specified Dimensions Are Shown For Reference Only!

DRAWN BY:	DATE:
Jeff McVicker	9/24/97
CHECKED BY:	DATE:
JOHN COLE	10/10/97
APPROVED BY:	DATE:
BRETT BRAATZ	10/14/97

DRAWING TITLE:			
Hex Nylon Tapped Spacers			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-124	ta-124.dwg	B
SCALE: NTS		U.O.M.: INCHES [mm]	SHEET: 1 OF 1