

90° LED ASSEMBLIES


Bi-Color, Bi-Level Assemblies

- Low Cost and Space Saving Design
- Standard Footprint



- Interlocking Versions Available
- Additional Configurations

H-201CBC Series

T-1 (3mm) Bi-Level Assembly.



LED Assy. No.	Peak Wave Length	Emitted Color	Lens Appearance	Abs. Max. Rating If (mA)	Electro-Optical Data @20mA			Viewing Angle 2 θ 1/2 (deg)	LED P/N
					Vf (V)	Iv (mcd)			
H201CBC	635	HE RED	WHITE	30	2.0	2.6	30.0	45	3BC
	568	GREEN	DIFFUSED	30	2.2	2.6	30.0		
H201CBC-Y/G	585	YELLOW	WHITE	30	2.1	2.6	15.0	45	3BC-Y/G
	568	GREEN	DIFFUSED	30	2.2	2.6	30.0		



H-278CBC Series

T-1^{3/4} (5mm) Bi-Level Assembly.



LED Assy. No.	Peak Wave Length	Emitted Color	Lens Appearance	Abs. Max. Rating If (mA)	Electro-Optical Data @20mA			Viewing Angle 2 θ 1/2 (deg)	LED P/N
					Vf (V)	Iv (mcd)			
H278CBC	635	HE RED	WHITE	30	2.0	2.6	45.0	50	5BC
	568	GREEN	DIFFUSED	30	2.2	2.6	45.0		
H278CBC-Y/G	585	YELLOW	WHITE	30	2.1	2.6	40.0	50	5BC-Y/G
	568	GREEN	DIFFUSED	30	2.2	2.6	40.0		

