

## Product Information

ingun Prüfmittelbau GmbH  
Max-Stromeyer-Straße 162  
78467 Konstanz  
Germany

Tel. +49 7531 8105-0  
Fax +49 7531 8105-65  
info@ingun.com  
www.ingun.com

## GKS-854 Test Probe compatible to series HSS-150

To bridge the gap of replaceable standard Test Probes (GKS) and High-current Probes (HSS) the series GKS-854 has been developed. With this, the following matching pairs are available: GKS-112 / HSS-118, GKS-113 / HSS-120 and GKS-854 / HSS-150.

The Probe series GKS-854 has the same, basic design as the series HSS-150 and is therefore 100% compatible. Apart from this, the series GKS-854 is available both in the normal plug-in version as well as the screw-in GKS-854 M version. It is used together with the Receptacle from the series HSS-150 / HSS-150 M.


### Mechanical Data:

Working Stroke:	4.4 mm
Max. Stroke:	5.5 mm
Spring Force at Working Stroke:	5.0 N + 15% alternative 3.0 N
Installation Height: with Receptacle	10.8 mm

### Electrical Data:

Rated Current:	10 - 12 A
Ri typical:	< 100 mOhm

Prices and delivery times on request.  
Technical changes possible.



### Ordering Example:

	Serie	Tip Materials 3 = BeCu	Tip Style	Tip Diameter ( <sup>1</sup> /100 mm)	Plating A = Gold	Spring Force (dN)	Collar Height (mm)	Type alternative "MC"
Test Probe:			G K S	8 5 4	3 1 9	4 0 0	A 5 0	0 2 C
Receptacle:			K S - 1 5 0					