

HC-WRV-PG21

Order No.: 1666825



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1666825>

Corrugated tube screw connection, for corrugated tube, to lead individual conductors and wires with IP65 protection into the housings of the industrial connectors HEAVYCON, type Pg21

Commercial data

GTIN (EAN)	4 017918 136925
sales group	D096
Pack	10 pcs.
Customs tariff	39174000
Catalog page information	Page 557 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
10/31/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Cable gland material	PA
Inflammability class acc. to UL 94	HB
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 110 °C

Certificates / Approvals



Certification

GOST

Diagrams/Drawings

Dimensioned drawing

Assembly instructions for Pg21 corrugated pipe

a = Corrugated screw connection

B = Corrugated pipe

c = Opener

Installation note:

Cut the corrugated pipe in the groove to retain a round shape for insertion. The lighter seal (not depicted in the illustration) is positioned in the corrugated pipe screw connection below the safety latch. The darker outer seal (not depicted in the illustration) is placed over the corrugated pipe screw connection from outside. The corrugated pipe is then pushed as far as possible into the corrugated pipe screw connection and clicks into place. The screw connection is opened by placing the yellow corrugated pipe opener with force between the safety latch and the corrugated tube and the corrugated pipe is then pulled out.

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;