


Part Number: AG1260-0
Normally Open Tip Over Switch
Product Data Sheet

PICTURE



✓ RoHS Compliant


OPERATION



FEATURES

- Resistant to Ambient Environmental Conditions
- Case Material : Tin Plated
- Mechanical Stress Resistant
- Antivibration Feature
- Hermetically Sealed & Inert Gas Filled

DIMENSIONS



Drawings not to scale.

All dimensions in inches (mm) nominal.

SPECIFICATION

Contact Capacity	3VA MAX
Contact Resistance	6 Ohms MAX at 5V DC
Make Angle	50°-70°
Operating Temperature	-38° +100°C

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

Phone: (1) 973 777 6900

www.comus-intl.com

Fax: (1) 973 777 8405