




DESCRIPTION: **LOW PROFILE FLAT RIBBON CONNECTOR**



	A	B	C NO S/R	C WITH S/R
9	1.213 30.81	.984 25.00	.610 15.49	.730 18.54
15	1.541 39.14	1.312 33.33	.610 15.49	.730 18.54
25	2.088 53.04	1.852 47.04	.610 15.49	.730 18.54
37	2.729 69.32	2.500 63.50	.610 15.49	.730 18.54



TERMINATED



184-XXX-X92-XX1

SERIES _____
POSITIONS _____
009
015
025
037
050
GENDER _____
1 = MALE
2 = FEMALE
TERMINATION _____
9 = IDC
SHELL PLATING _____
2 = TIN/ZINC
HARDWARE OPTIONS _____
00 = NO HARDWARE
01 = .065 4-40 CLINCH NUT BOARD SIDE
02 = .250 4-40 CLINCH NUT BOARD SIDE
03 = .250 4-40 CLINCH NUT MATING SIDE
PLATING OPTIONS _____
1 = GOLD FLASH

SPECIFICATIONS:

MATERIALS:

SHELL: STEEL, TIN OR ZINC PLATED
INSULATOR: UL 94V-0 RATED PBT
+30% FIBER-GLASS OR NYLON-66

ELECTRICALS:


CURRENT RATING: 1 AMP
CONTACT RESISTANCE: 15 mOHMS MAX
INSULTOR RESISTANCE: 1000 MOHMS MIN
VOLTAGE: 500V AC FOR 1 MINUTE
TEMPERATURE: -50°C TO +100°C

ACCEPTS: 28 AWG SOLID OR STRANDED .050" CENTER FLAT RIBBON CABLE


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: WAYNE ROBBINS		DATE: 9-28-98	
	NorComp		CHECKED:		DATE:	
			SCALE: 1:1		SHEET 1 OF 1	
		DWG NO.		184-XXX-192-XX1		
				REV 4		

DESCRIPTION: CLINCH NUT HARDWARE


ALL CLINCH-NUTS ARE 4-40 INTERNAL THREADS




03X..... .250" (MATING SIDE) - CN8



02X250" (BOARD SIDE) - CN2



01X065" (BOARD SIDE) - CN1



91X225" (BOARD SIDE) - .197 MATING SIDE - CN10/SFS0440
NOTE: 4-40 FEMALE SCREW LOCK IS REMOVABLE

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: WAYNE ROBBINS		DATE: 8-23-98	
		CHECKED: PAM JENKINS		DATE: 8-24-98	
		SCALE:	SHEET 1 OF 1		REV 3
		DWG NO. CLINCH-NUT OPTIONS			