


REV.	DATE	DESCRIPTION
A	12/09/03	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex										
8						DRAWN	G.R.S.							12/09/03				
7						CHECKED									PART DESCRIPTION			
6							ISSUED			SMB BULKHEAD RECESSED RECEPT. JACK								
5	HEX NUT	BRASS	NICKEL	1						PART NO.								
4	LOCK WASHER	BRASS	NICKEL	1						142156								
3	CONTACT PIN	BRASS	GOLD	1														
2	INSULATOR	TEFLON	NATURAL	1														
1	BODY	BRASS	NICKEL	1														
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE	C:/142/142156.DWG			DWG. NO.	142156.DWG		REV.	NC	SIZE	A	SCALE	NA