



842 ERSADUR Long-Life Soldering Tip Series

For:

- **ANALOG 60 / 60 A**
- **ANALOG 80 / 80 A**
- **DIGITAL 80 A**
- **DIGITAL 2000 A**
with Power tool soldering iron
- **ELS 8000 / M / D**
- **MICRO-CON 60 iA**
with Power tool soldering iron
- **MS 6000**
- **MS 8000 / D**
- **Multi-Pro**
- **Multi-Sprint**
- **Multi-TC**
- **RDS 80**
- **TWIN 80 A**
with Ergo tool soldering iron




0842UD / UDLF <i>pencil point, extended, 0.4 mm ø</i>	0842SD / SDLF <i>pencil point, extended, 0.8 mm ø</i>	0842BD / BDLF <i>pencil point, 1.0 mm ø</i>
0842YD / YDLF <i>chisel-shaped, 1.6 mm</i>	0842CD / CDLF <i>chisel-shaped, 2.2 mm</i>	0842KD / KDLF <i>chisel-shaped, extended, 2.2 mm</i>
0842ED / EDLF <i>chisel-shaped, 3.2 mm</i>	0842ID <i>pencil point, bent, 0.4 mm ø</i>	0842JD <i>chisel-shaped, bent, 2.2 mm</i>

722 Desoldering Tip Series, ERSADUR / nickel-plated

For:

- **DIGITAL 2000 A**
with X-Tool desoldering iron
- **XTOOLKIT1**



0722ED1023 <i>ERSADUR, ID 1.0 mm, OD 2.3 mm</i>	0722EN0615S <i>nickel-plated, ID 0.6 mm, OD 1.5 mm</i>	0722EN1018S <i>nickel-plated, ID 1.0 mm, OD 1.8 mm</i>
0722ED0821 ERSADUR, ID 0.8 mm, OD 2.1 mm 	0722EN0818 nickel-plated, ID 0.8 mm, OD 1.8 mm 	0722EN1020 nickel-plated, ID 1.0 mm, OD 2.0 mm
0722ED1529 ERSADUR, ID 1.5 mm, OD 2.9 mm 	0722EN0823 nickel-plated, ID 0.8 mm, OD 2.3 mm 	0722EN1023 nickel-plated, ID 1.0 mm, OD 2.3 mm
0722EN1223 nickel-plated, ID 1.2 mm, OD 2.3 mm 	0722EN1529 nickel-plated, ID 1.5 mm, OD 2.9 mm 	0722EN2332 nickel-plated, ID 2.3 mm, OD 3.2 mm
0722ED1226 ERSADUR, ID 1.2 mm, OD 2.6 mm 	0722EN1548 nickel-plated, ID 1.5 mm, OD 4.8 mm 	0722EN2348 nickel-plated, ID 2.3 mm, OD 4.8 mm