






No	Symbol	No	Symbol
1	VLED+	26	G1
2	VLED+	27	G0
3	VLED-	28	R7
4	VLED-	29	R6
5	GND	30	R5
6	VCOM	31	R4
7	DVDD	32	R3
8	MODE	33	R2
9	DE	34	R1
10	V5	35	R0
11	H5	36	GND
12	B7	37	OCUK
13	B6	38	GND
14	B5	39	L/R
15	B4	40	U/D
16	B3	41	VGH
17	B2	42	VGL
18	B1	43	AVDD
19	B0	44	RESET
20	G7	45	NC
21	G6	46	VCOM
22	G5	47	DITHB
23	G4	48	GND
24	G3	49	NC
25	G2	50	NC

NOTES:

- 1.DISPLAY TYPE: a-Si TFT
- 2.DISPLAY MODULE: Transmissive ,Normally White
- 3.OPERATIN TEMP: -20° C---+70° C
- 4.STORAGE TEMP: -30° C---+80° C
- 5.Backlight: LED
6. RoHS Complicant

pin No.	name
TP-PIN1	VDD
TP-PIN2	NC
TP-PIN3	NC
TP-PIN4	NC
TP-PIN5	GND
TP-PIN6	VDD
TP-PIN7	INT
TP-PIN8	RST
TP-PIN9	SCL
TP-PIN10	SDA

GHI Electronics
www.ghielectronics.com

DRAWN BY:	TITLE: TFTCP-GP-386		
CHECKED BY:			
APPROVED BY:	DWG NO:	SCALE:	
CONFIRMED BY:	DWG NAME:	SHEET NO: 01	UNIT: mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[GHI Electronics:](#)

[DSCP7-GM-376](#)