



	10	9	8	7	6	5	4	3	2	1																																													
	MATERIAL NO	OPTIONAL SUB ASSY	PLT REF	DIM M	DIM G	CKT SIZE	VOID CKT #	KINKED PIN	PICK & PLACE CAP	CUT PIN CKT NO.																																													
F	68301-1007	42375-0010	154	.240 6.10	.433 10.99	10	NONE	NONE	YES	-	F																																												
	68301-1109	42375-0115	154	.320 8.13	-	10	NONE	NONE	-	-																																													
	68301-1159 	42375-0116	154	.320 8.13	.513 13.02	11	NONE	NONE	YES	-																																													
	68301-1063	-	154	.240 6.10	-	12	NONE	NONE	-	-																																													
	68301-1111	42375-0117	154	.320 8.13	-	12	NONE	NONE	-	-																																													
	68301-1157	NONE	208	.605 15.37	-	12	NONE	NONE	-	-																																													
E	68301-1065	42375-0014	154	.240 6.10	-	14	NONE	NONE	-	-	E																																												
	68301-1129	42375-0154	208	.320 8.13	-	14	NONE	NONE	-	-																																													
	68301-1113	42375-0121	154	.320 8.13	-	14	NONE	NONE	-	-																																													
	68301-1066	42375-0015	154	.240 6.10	-	15	NONE	NONE	-	-																																													
	68301-1067	42375-0016	154	.240 6.10	-	16	NONE	NONE	-	-																																													
	68301-1115	42375-0121	154	.320 8.13	-	16	NONE	NONE	-	-																																													
D	68301-1069	42375-0018	154	.240 6.10	-	18	NONE	NONE	-	-	D																																												
	68301-1117	42375-0123	154	.320 8.13	-	18	NONE	NONE	-	-																																													
	68301-1119	42375-0125	154	.320 8.13	-	20	NONE	NONE	-	-																																													
	68301-1071	42375-0020	154	.240 6.10	-	20	NONE	NONE	-	-																																													
	68301-1072	42375-0021	154	.240 6.10	-	21	NONE	NONE	-	-																																													
	68301-1123	42375-0129	154	.320 8.13	-	24	NONE	NONE	-	-																																													
C											C																																												
B											B																																												
A											A																																												
<table><tr><td rowspan="5">ADD T&R P/N 68301-0400 EC NO: S2009-0634 DRWN:SKANG 2009/04/06 CHKD:ATSEE 2009/04/06 APPR:MLONG 2009/04/14 M6</td><td rowspan="5">REV</td><td rowspan="5">DESCRIPTION</td><td rowspan="5">QUALITY SYMBOLS ▽=0 ▽=0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE IN/MM</td><td>SCALE NTS</td><td>DESIGN UNITS INCH</td><td rowspan="5"> THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="4">4 PLACES</td><td>± ---</td><td>± ---</td><td rowspan="4">DRAWN BY SAMIAC</td><td>DATE 2000/10/28</td><td rowspan="4">TITLE CUSTOM HEADER .100/(2.54) CENTERLINE VERTICAL/SMT SINGLE ROW MOLEX INCORPORATED</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± .005</td><td>CHECKED BY SAMIEC</td><td>DATE 2000/10/28</td></tr><tr><td>2 PLACES</td><td>± 0.13</td><td>± .010</td><td>APPROVED BY EDGLEY</td><td>DATE 2000/10/28</td></tr><tr><td>1 PLACE</td><td>± 0.25</td><td>± ---</td><td>MATERIAL NO. SEE TABLE</td><td>DOCUMENT NO. SD-68301-001</td><td>SHEET NO. 2 OF 5</td></tr><tr><td colspan="4">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">ANGULAR ±1/2°</td><td colspan="2">SIZE A3</td><td colspan="3">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>												ADD T&R P/N 68301-0400 EC NO: S2009-0634 DRWN:SKANG 2009/04/06 CHKD:ATSEE 2009/04/06 APPR:MLONG 2009/04/14 M6	REV	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE NTS	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	4 PLACES	± ---	± ---	DRAWN BY SAMIAC	DATE 2000/10/28	TITLE CUSTOM HEADER .100/(2.54) CENTERLINE VERTICAL/SMT SINGLE ROW MOLEX INCORPORATED	3 PLACES	± ---	± .005	CHECKED BY SAMIEC	DATE 2000/10/28	2 PLACES	± 0.13	± .010	APPROVED BY EDGLEY	DATE 2000/10/28	1 PLACE	± 0.25	± ---	MATERIAL NO. SEE TABLE	DOCUMENT NO. SD-68301-001	SHEET NO. 2 OF 5	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				ANGULAR ±1/2°		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
ADD T&R P/N 68301-0400 EC NO: S2009-0634 DRWN:SKANG 2009/04/06 CHKD:ATSEE 2009/04/06 APPR:MLONG 2009/04/14 M6	REV	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE NTS	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION																																													
				4 PLACES	± ---	± ---	DRAWN BY SAMIAC	DATE 2000/10/28	TITLE CUSTOM HEADER .100/(2.54) CENTERLINE VERTICAL/SMT SINGLE ROW MOLEX INCORPORATED																																														
					3 PLACES	± ---		± .005			CHECKED BY SAMIEC					DATE 2000/10/28																																							
					2 PLACES	± 0.13		± .010			APPROVED BY EDGLEY					DATE 2000/10/28																																							
					1 PLACE	± 0.25		± ---			MATERIAL NO. SEE TABLE	DOCUMENT NO. SD-68301-001	SHEET NO. 2 OF 5																																										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				ANGULAR ±1/2°		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																															
tb_frame_A3_P_AM_T Rev. E 2006/04/15	9	8	7	6	5	4	3	2	1																																														

	10		9		8		7		6		5		4		3		2		1		
F	MATERIAL NO.	OPTIONAL SUB ASSY	PLT REF	DIM M	DIM G	CKT SIZE	VOID CKT #	KINKED PIN	PICK & PLACE CAP	CUT PIN CKT NO.										F	
	68301-1054	42375-0002	154	.240 6.10	-	2	NONE	NONE	-	-											
	68301-1055	42375-0037	208	.240 6.10	-	2	NONE	NONE	-	-											
	68301-1056	42375-0072	228	.240 6.10	-	2	NONE	NONE	-	-											
	68301-1051	42375-0107	154	.320 8.13	-	2	NONE	NONE	-	-											
	68301-1009	42375-0038	208	.240 6.10	-	3	NONE	NONE	-	-											
	68301-1014	42375-0003	154	.240 6.10	-	3	NONE	NONE	-	-											
E	68301-1020	42375-0073	228	.240 6.10	-	3	NONE	NONE	-	-										E	
	68301-1031	42375-0108	154	.320 8.13	-	3	NONE	NONE	-	-											
	68301-1037	42375-0143	208	.320 8.13	-	3	NONE	NONE	-	-											
	68301-1010	42375-0039	208	.240 6.10	-	4	NONE	NONE	-	-											
	68301-1015	42375-0004	154	.240 6.10	-	4	NONE	NONE	-	-											
	68301-1021	42375-0074	228	.240 6.10	-	4	NONE	NONE	-	-											
D	68301-1032	42375-0109	154	.320 8.13	-	4	NONE	NONE	-	-										D	
	68301-0400	-	228	.320 8.13	.513 13.02	4	NONE	NONE	YES	-											
	68301-1038	42375-0144	208	.320 8.13	-	4	NONE	NONE	-	-											
	68301-1006	42375-0040	208	.240 6.10	-	5	NONE	NONE	-	-											
	68301-1016	42375-0005	154	.240 6.10	-	5	NONE	NONE	-	-											
	68301-1033	42375-0110	154	.320 8.13	-	5	NONE	NONE	-	-											
C	68301-1039	42375-0145	208	.320 8.13	-	5	NONE	NONE	-	-										C	
B																					B
A																					A
tb_frame_A3_P_AM_T Rev. F 2006/04/15		9	8	7	6	5	4	3	2	1											
ADD T&R P/N 68301-0400 EC NO: S2009-0634 DRWN:SKANG 2009/04/04 CHKD:ATSEE 2009/04/06 APPR:MLONG 2009/04/14 M6		REV		QUALITY SYMBOLS ▽=0 ▽C=0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .005 2 PLACES ± 0.13 ± .010 1 PLACE ± 0.25 ± --- ANGULAR ± 1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION STYLE IN/MM DRAWN BY DATE SAMIAC 2000/10/28 CHECKED BY DATE SAMIEC 2000/10/28 APPROVED BY DATE EDGLEY 2000/10/28 MATERIAL NO. SEE TABLE		SCALE NTS TITLE CUSTOM HEADER .100/(2.54) CENTERLINE VERTICAL/SMT SINGLE ROW MOLEX INCORPORATED DOCUMENT NO. SD-68301-001		DESIGN UNITS INCH THIRD ANGLE PROJECTION		SHEET NO. 3 OF 5							
SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			

10		9		8		7		6		5		4		3		2		1																																																			
ASSEMBLY IN TUBE		ASSEMBLY IN T&R WITH CAP		OPTIONAL SUB ASSY		PLT REF		DIM M		DIM G		CKT SIZE		VOID CKT #		KINKED PIN		PICK & PLACE CAP		CUT PIN CKT NO.																																																	
F	68301-1011	-		42375-0041		208		.240 6.10		-		6		NONE		NONE		-		-																																																	
	68301-1017	-		42375-0006		154		.240 6.10		-		6		NONE		NONE		-		-																																																	
	68301-1034	68301-1160		42375-0111		154		.320 8.13		.513 13.02		6		NONE		NONE		YES		-																																																	
	68301-1040	-		42375-0146		208		.320 8.13		-		6		NONE		NONE		-		-																																																	
E	68301-1023	-		42375-0076		228		.240 6.10		-		6		NONE		NONE		-		-																																																	
	68301-1012	-		42375-0042		208		.240 6.10		-		7		NONE		NONE		-		-																																																	
	68301-1018	-		42375-0007		154		.240 6.10		-		7		NONE		NONE		-		-																																																	
	68301-1035	-		42375-0112		154		.320 8.13		-		7		NONE		NONE		-		-																																																	
D	68301-1041	-		42375-0147		208		.320 8.13		-		7		NONE		NONE		-		-																																																	
	68301-1013	-		42375-0043		208		.240 6.10		-		8		NONE		NONE		-		-																																																	
	68301-1029	-		-		228		.240 6.10		-		8		NONE		NONE		-		-																																																	
	68301-1019	-		42375-0008		154		.240 6.10		-		8		NONE		NONE		-		-																																																	
C	68301-1028	-		-		228		.505 12.83		-		8		NONE		NONE		-		-																																																	
	68301-1036	-		42375-0113		154		.320 8.13		-		8		NONE		NONE		-		-																																																	
	68301-1042	-		42375-0148		208		.320 8.13		-		8		NONE		NONE		-		-																																																	
	68301-0800	-		-		208		.605 15.37		-		8		NONE		NONE		-		-																																																	
B	68301-1076	-		42375-0044		208		.240 6.10		-		9		NONE		NONE		-		-																																																	
	68301-1060	-		-		154		.240 6.10		-		9		NONE		NONE		-		-																																																	
A	ADD T&R P/N 68301-0400 EC NO: S2009-0634 DRWN:SKANG CHKD:ATSEE APPR:MLONG 2009/04/01 2009/04/06 2009/04/14 DESCRIPTION REV QUALITY SYMBOLS ▼=0 ◻=0 GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± .005</td></tr><tr><td>2 PLACES</td><td>± 0.13</td><td>± .010</td></tr><tr><td>1 PLACE</td><td>± 0.25</td><td>± ---</td></tr><tr><td colspan="3">ANGULAR ±1/2°</td></tr></table> DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DIMENSION STYLE IN/MM <table><tr><td>DRAWN BY</td><td>DATE</td></tr><tr><td>SAMIAC</td><td>2000/10/28</td></tr><tr><td>CHECKED BY</td><td>DATE</td></tr><tr><td>SAMIEC</td><td>2000/10/28</td></tr><tr><td>APPROVED BY</td><td>DATE</td></tr><tr><td>EDGLEY</td><td>2000/10/28</td></tr></table> MATERIAL NO. SEE TABLE SCALE NTS DESIGN UNITS INCH THIRD ANGLE PROJECTION CUSTOM HEADER .100/(2.54) CENTERLINE VERTICAL/SMT SINGLE ROW MOLEX INCORPORATED SD-68301-001 SHEET NO. 4 OF 5 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																						mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± .005	2 PLACES	± 0.13	± .010	1 PLACE	± 0.25	± ---	ANGULAR ±1/2°			DRAWN BY	DATE	SAMIAC	2000/10/28	CHECKED BY	DATE	SAMIEC	2000/10/28	APPROVED BY	DATE	EDGLEY	2000/10/28	9		8		7		6		5		4		3		2		1	
		mm	INCH																																																																		
4 PLACES	± ---	± ---																																																																			
3 PLACES	± ---	± .005																																																																			
2 PLACES	± 0.13	± .010																																																																			
1 PLACE	± 0.25	± ---																																																																			
ANGULAR ±1/2°																																																																					
DRAWN BY	DATE																																																																				
SAMIAC	2000/10/28																																																																				
CHECKED BY	DATE																																																																				
SAMIEC	2000/10/28																																																																				
APPROVED BY	DATE																																																																				
EDGLEY	2000/10/28																																																																				
tb_frame_A3_P_AM_T																																																																					
Rev. E 2006/04/15																																																																					

CKT SIZE	QTY/ REEL	Ao	Ko	F	So	W	TYPE
4	TBD	4.85	13.40	11.50	-	24.00	B
6	230	4.85	13.40	14.20	28.40	32.00	A
10	230	4.90	11.30	20.20	40.40	44.00	A


EMBOSSED TYPE A



SECTION Z-Z

NOTES:

1. LEADER AND TRAILER TAPE




2. PEELING OFF FORCE OF THE TOP TAPE: 60gf MAX.
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIGURE)



- 3. THE TAPE IS TREATED FOR ANTI ESD
- 4. PACKAGING STANDARD AS PER EIA-481.
- 5. ABOVE PACKAGING ILLUSTRATION IS FOR 6CKT ONLY.

EMBOSSED TYPE B



CUSTOMER PULL
OUT DIRECTION

ADD T&R P/N 68301-0400 EC NO: S2009-0634 DRWN:KANG CHKD:ATSEE APPR:MLONG M6	QUALITY SYMBOLS ▽=0 ◻=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY SAMIAC	DATE 2000/10/28	TITLE CUSTOM HEADER .100/(2.54) CENTERLINE VERTICAL/SMT SINGLE ROW MOLEX INCORPORATED	DOCUMENT NO. SD-68301-001	SHEET NO. 5 OF 5	
			4 PLACES	± ---	± ---	CHECKED BY	DATE				
			3 PLACES	± ---	± .005	SAMI EC	2000/10/28				
			2 PLACES	± 0.13	± .010	APPROVED BY	DATE				
	1 PLACE	± 0.25	± ---	EDGLE Y	2000/10/28						
			ANGULAR ±1/2°		MATERIAL NO.						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE						
		REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					