

5

4

3

2




1

D

C

B

A



Part number	$\phi D1$ (mm)	$\phi D2$ (mm)
61 03 000 0107	16,0	17,0
61 03 000 0106	14,5	15,5
61 03 000 0061	14,0	15,0
61 03 000 0060	13,7	15,0
61 03 000 0127	13,0	14,0
61 03 000 0059	12,5	13,5
61 03 000 0142	12,0	13,0
61 03 000 0058	11,5	12,5
61 03 000 0057	11,0	12,0
61 03 000 0056	10,5	11,5
61 03 000 0055	10,0	11,0
61 03 000 0054	9,5	10,5
61 03 000 0053	9,0	10,0
61 03 000 0052	8,5	9,5
61 03 000 0051	8,0	9,0
61 03 000 0050	7,5	8,5
61 03 000 0049	7,0	8,0
61 03 000 0048	6,5	7,5
61 03 000 0047	6,0	7,0
61 03 000 0046	5,5	6,5
61 03 000 0045	5,0	6,0

			Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	INDUCOM Crimp ferrules	Maßstab/ Scale
			Detail.	13/04/04			HAGE
			Insp.			TB 61 03 000 OYYY	Blatt/ Page 1 / 1
EC00995	19/10/09	PK	Stand.				
32093	30/06/04	HAGE	HARTING EURL F-95972 Paris				
31987			Mod.	Dot.			
						Sub.	