






REV.	DATE	ECR NO.	DESCRIPTION
NC	02/24/02	—	INITIAL RELEASE
A	03/26/09	100089	UPDATE DRAWING FORMAT, ADD TOLERANCES TO MOUNTING HOLE DIMS.



RECOMMENDED
MOUNTING HOLE



NOTE:

1. MAX. PANEL THICKNESS = 6.6mm

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex							
8						DRAWN	GRS								03/26/09
7						CHECKED			PART DESCRIPTION SMA JACK TO BNC BULKHEAD JACK ADAPTER						
6	HEX NUT	BRASS	NICKEL	1		ISSUED									
5	LOCK WASHER	PHOS. BRONZE	NICKEL	1		SHEET	1 OF 1		PART NO. 242181						
4	GASKET	SILICONE	RED	1											
3	CONTACT PIN	BER. COPPER	GOLD	1				DWG. NO. 242181.DWG							
2	INSULATOR	PTFE	NATURAL	1											
1	BODY	BRASS	NICKEL	1				REV.	NC	SIZE	A	SCALE	NA		
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE								