




**Frequency Response**



The APart MICPAT-D is a sturdy table type paging microphone.

It has a flexible stem and a high quality unidirectional dynamic microphone capsule. The paging microphone is intended for making calls to all zones (i.e. All-Call).

The microphone has a stable aluminium base, equipped with a toggle switch that has following positions:

- Up: Continuous talk
- Mid: Off
- Down: pull to talk

The microphone comes with a DIN5 connector.

## TECHNICAL SPECIFICATIONS

|                        |                                             |
|------------------------|---------------------------------------------|
| Type                   | Table type                                  |
| Polar pattern          | Uni-directional                             |
| Frequency range        | 80 Hz - 12 kHz                              |
| Sensitivity            | -70 dB @ 1 kHz                              |
| Rated output impedance | 600 Ohm                                     |
| Switch                 | Toggle switch; Talk - OFF - Continuous Talk |
| Cable                  |                                             |
| Type                   | 2 core + 2 core screened                    |
| Length                 | 3 m                                         |
| Connector              | 5-pole DIN                                  |
| Material               | One piece mold, aluminium base              |
| Weight (incl. cable)   | 0.81 Kg                                     |

**Dimensions**

