




- 1 NYLON OR POLYESTER, UL 94V-0 RATED, COLOR: SEE TABLE.
- 2 RECOMMENDED WIRE: 28 AWG OR 30 AWG SOLID OR 7 STRAND. SEE TABLE FOR INSULATION DIA. WIRE MUST BE APPROVED BY AMP INC.
3. TWO COVERS REQUIRED PER CONNECTOR ASSEMBLY.
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	0.74-0.79	[.029-.031]	GRAY	2	62.23	[2.450]	63.86	[2.514]	71.50	[2.815]	100	1-750877-9
	0.74-0.79	[.029-.031]	GRAY	2	41.91	[1.650]	43.54	[1.714]	51.18	[2.015]	68	1-750877-7
	0.74-0.79	[.029-.031]	GRAY	2	30.48	[1.200]	32.11	[1.264]	39.75	[1.565]	50	1-750877-5
4 OBSOLETE	0.74-0.79	[.029-.031]	GRAY	2	24.13	[.950]	25.76	[1.014]	33.40	[1.315]	40	1-750877-4
	0.74-0.79	[.029-.031]	GRAY	2	15.24	[.600]	16.87	[.664]	24.51	[.965]	26	1-750877-2
4 OBSOLETE	0.81-0.91	[.032-.036]	BLACK	1	62.23	[2.450]	63.86	[2.514]	71.50	[2.815]	100	750877-9
OBSOLETE	0.81-0.91	[.032-.036]	BLACK	1	49.53	[1.950]	51.156	[2.014]	58.801	[2.315]	80	750877-8
	0.81-0.91	[.032-.036]	BLACK	1	41.91	[1.650]	43.54	[1.714]	51.18	[2.015]	68	750877-7
	0.81-0.91	[.032-.036]	BLACK	1	30.48	[1.200]	32.11	[1.264]	39.75	[1.565]	50	750877-5
4 OBSOLETE	0.81-0.91	[.032-.036]	BLACK	1	24.13	[.950]	25.76	[1.014]	33.40	[1.315]	40	750877-4
	0.81-0.91	[.032-.036]	BLACK	1	15.24	[.600]	16.87	[.664]	24.51	[.965]	26	750877-2
	WIRE OUTER DIA		COLOR	PART ID NO	C	B	A	NO OF POSN	PART NUMBER			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 單位： 毫米 mm[INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差

0 PLC ± -

1 PLC ± -

2 PLC ± 0.13 [.005]

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL 材料

FINISH 仕上

DWN B. MCMASTER 14JUNE04

CHK S. SHUEY 14JUNE04

APVD M. WALMSLEY 14JUNE04

PRODUCT SPEC 製品規格

APPLICATION SPEC 取付適用規格

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

COVER, TERMINATING, DISCRETE WIRE, AMPLIMITE

SIZE A2

CAGE CODE 00779

DRAWING NO 番号 G-750877

RESTRICTED TO -

SCALE 尺度 8:1

SHEET 1 OF 1

REV E