



LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				B	REVISED & REDRAWN PER 0720-0044-94	4/29/94	OK DAP



- 1

STAMP AMP APPROX AS SHOWN
- 2

MAXIMUM LENGTH DOES NOT INCLUDE MANUFACTURING TABS
- 3

GOLD PLATE 0.00127[.000050] MIN THK PER MIL-G-45204 OVER NICKEL PLATE 0.00762[.000030] MIN THK PER QQ-N-290

AMP WIRE RANGE	E13288 Listed
24-20 AWG SOLID OR STRANDED	NOT LISTED
LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

FOR APPLICATION
TOOLING INFORMATION

FOR ORDER ENTRY

PRODUCT INFORMATION CENTER
1-800-522-6752

TOOLING ASSISTANCE CENTER
1-800-722-1111

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
0.16-0.65mm² [320-1,290] CIR MILS
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± -
3 PLC DEC ± -
ANGLES ± -
MATERIAL
COPPER PER
ASTM B-152
ANNEALED

FINISH



DR 4/29/94
DK SCHRUM
CHK 5/5/94
DA PATTERSON
APPD 5/5/94
CH KULYNYCH
APPD 5/5/94
JL MECKLEY
PRODUCT SPEC
-

APPLICATION SPEC

WEIGHT -

-	LOOSE PIECE, BOX	328588
QTY	PACKAGE TYPE	PART NO
AMP AMP Incorporated Harrisburg, PA 17105-3608		
NAME SPLICE, BUTT, STRAP, SOLISTRAND™		
SIZE	CAGE CODE	DRAWING NO
C	00779	C=328588
SCALE	10:1	SHEET 1 OF 1