

## A. System Overview

### Pre-Printed Marker Cards PCM Type

- Marker cards printed in a variety of legends allows “kitting” for project builds


- Plastic liner provides easy removal of markers while protecting unused markers

## B1. Cable Ties

## B2. Cable Accessories

## B3. Stainless Steel Ties

### Material Chart



| Material           | Print Method | Temperature Range                 | Features                                                                                                                                                                                                                                                                               |
|--------------------|--------------|-----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Vinyl Cloth, White | Pre-Printed  | -50°F to 170°F<br>(-46°C to 77°C) | Indoor/outdoor rated; conformable material with repositionable adhesive allows label to be removed and reused or used in temporary applications; provides durability, high temperature resistance, and dimensional stability for rough or textured surfaces; resists oil and abrasion. |

## C1. Wiring Duct

## C2. Surface Raceway

## C3. Abrasion Protection

## C4. Cable Management

## D1. Terminals

## D2. Power Connectors

## D3. Grounding Connectors

## E1. Labeling Systems

## E2. Labels

## E3. Pre-Printed & Write-On Markers


## E4. Permanent Identification

## E5. Lockout/Tagout & Safety Solutions

## F. Index



PCM-7



PCM-1-6

| Part Number | Legend       | Width |      | Length |       | Markers Per Card | Std. Pkg. Card(s) | Std. Ctn. Card(s) |
|-------------|--------------|-------|------|--------|-------|------------------|-------------------|-------------------|
|             |              | In.   | mm   | In.    | mm    |                  |                   |                   |
| PCM-0       | 0            | 0.25  | 6.35 | 1.50   | 38.1  | 36               | 25                | 100               |
| thru        | thru         |       |      |        |       |                  |                   |                   |
| PCM-99      | 99           |       |      |        |       |                  |                   |                   |
| PCM-100     | 100          | 0.36  | 9.14 | 1.50   | 38.1  | 25               | 25                | 100               |
| thru        | thru         |       |      |        |       |                  |                   |                   |
| PCM-202     | 202          |       |      |        |       |                  |                   |                   |
| PCMH-0      | 0            | 0.25  | 6.35 | 1.50   | 38.1  | 72               | 25                | 100               |
| thru        | thru         |       |      |        |       |                  |                   |                   |
| PCMH-25     | 25           |       |      |        |       |                  |                   |                   |
| PCM-1-3     | 1 thru 3     | 0.25  | 6.35 | 1.50   | 38.10 | 36               | 25                | 100               |
| PCM-1-4     | 1 thru 4     |       |      |        |       |                  | 25                | 100               |
| PCM-1-5     | 1 thru 5     |       |      |        |       |                  | 25                | 100               |
| PCM-1-6     | 1 thru 6     | 0.25  | 6.35 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-1-8     | 1 thru 8     | 0.25  | 6.35 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-1-9     | 1 thru 9     | 0.25  | 6.35 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-0-9     | 0 thru 9     | 0.25  | 6.35 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-1-10    | 1 thru 10    | 0.25  | 6.35 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-1-12    | 1 thru 12    | 0.25  | 6.35 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-1-16    | 1 thru 16    | 0.25  | 6.35 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-1-18    | 1 thru 18    | 0.25  | 6.35 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-19-36   | 19 thru 36   | 0.25  | 6.35 | 1.50   | 38.10 | 33               | 25                | 100               |
| PCM-1-33    | 1 thru 33    | 0.27  | 6.91 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-34-66   | 34 thru 66   | 0.27  | 6.91 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-67-99   | 67 thru 99   | 0.27  | 6.91 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-100-124 | 100 thru 124 | 0.36  | 9.14 | 1.50   | 38.10 | 25               | 25                | 100               |
| PCM-125-149 | 125 thru 149 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-150-174 | 150 thru 174 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-175-199 | 175 thru 199 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-200-224 | 200 thru 224 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-225-249 | 225 thru 249 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-250-274 | 250 thru 274 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-275-299 | 275 thru 299 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-300-324 | 300 thru 324 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-325-349 | 325 thru 349 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-350-374 | 350 thru 374 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-375-399 | 375 thru 399 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-400-424 | 400 thru 424 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-425-449 | 425 thru 449 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-450-474 | 450 thru 474 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-475-499 | 475 thru 499 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |
| PCM-500-524 | 500 thru 524 | 0.36  | 9.14 | 1.50   | 38.10 |                  | 25                | 100               |

## Pre-Printed Marker Cards PCM Type (continued)



PCM-A1

| Part Number              | Legend               | Width |      | Length |      | Markers<br>Per<br>Card | Std.<br>Pkg.<br>Card(s) | Std.<br>Ctn.<br>Card(s) |
|--------------------------|----------------------|-------|------|--------|------|------------------------|-------------------------|-------------------------|
|                          |                      | In.   | mm   | In.    | mm   |                        |                         |                         |
| PCM-A<br>thru<br>PCM-Z   | A<br>thru<br>Z       | 0.25  | 6.35 | 1.50   | 38.1 | 36                     | 25                      | 100                     |
| PCM-A-Z                  | A thru Z             | 0.25  | 6.35 | 1.50   | 38.1 |                        | 25                      | 100                     |
| PCM-A-Z-0-9              | A thru Z<br>0 thru 9 | 0.25  | 6.35 | 1.50   | 38.1 |                        | 25                      | 100                     |
| PCM-A1<br>thru<br>PCM-A4 | A1<br>thru<br>A4     | 0.25  | 6.35 | 1.50   | 38.1 |                        | 25                      | 100                     |
| PCM-B1<br>thru<br>PCM-B5 | B1<br>thru<br>B5     | 0.25  | 6.35 | 1.50   | 38.1 |                        | 25                      | 100                     |
| PCM-C1<br>thru<br>PCM-C4 | C1<br>thru<br>C4     | 0.25  | 6.35 | 1.50   | 38.1 |                        | 25                      | 100                     |
| PCM-E1<br>thru<br>PCM-E3 | E1<br>thru<br>E3     | 0.25  | 6.35 | 1.50   | 38.1 |                        | 25                      | 100                     |
| PCM-F1<br>thru<br>PCM-F4 | F1<br>thru<br>F4     | 0.25  | 6.35 | 1.50   | 38.1 |                        | 25                      | 100                     |
| PCM-H1<br>thru<br>PCM-H5 | H1<br>thru<br>H5     | 0.25  | 6.35 | 1.50   | 38.1 |                        | 25                      | 100                     |
| PCM-L1<br>thru<br>PCM-L5 | L1<br>thru<br>L5     | 0.25  | 6.35 | 1.50   | 38.1 |                        | 25                      | 100                     |
| PCM-M1<br>thru<br>PCM-M2 | M1<br>thru<br>M2     | 0.25  | 6.35 | 1.50   | 38.1 |                        | 25                      | 100                     |
| PCM-P1<br>thru<br>PCM-P3 | P1<br>thru<br>P3     | 0.25  | 6.35 | 1.50   | 38.1 |                        | 25                      | 100                     |
| PCM-R1<br>thru<br>PCM-R5 | R1<br>thru<br>R5     | 0.25  | 6.35 | 1.50   | 38.1 |                        | 25                      | 100                     |
| PCM-S1<br>thru<br>PCM-S5 | S1<br>thru<br>S5     | 0.25  | 6.35 | 1.50   | 38.1 |                        | 25                      | 100                     |
| PCM-T1<br>thru<br>PCM-T9 | T1<br>thru<br>T9     | 0.25  | 6.35 | 1.50   | 38.1 |                        | 25                      | 100                     |
| PCM-X1<br>thru<br>PCM-X4 | X1<br>thru<br>X4     | 0.25  | 6.35 | 1.50   | 38.1 |                        | 25                      | 100                     |

Table continues on page E3.6

A.  
System  
Overview

B1.  
Cable Ties

B2.  
Cable  
Accessories

B3.  
Stainless  
Steel Ties

C1.  
Wiring  
Duct

C2.  
Surface  
Raceway

C3.  
Abrasion  
Protection

C4.  
Cable  
Management

D1.  
Terminals

D2.  
Power  
Connectors

D3.  
Grounding  
Connectors

E1.  
Labeling  
Systems

E2.  
Labels

E3.  
Pre-Printed  
& Write-On  
Markers

E4.  
Permanent  
Identification

E5.  
Lockout/  
Tagout  
& Safety  
Solutions

F.  
Index

A.  
System  
Overview

B1.  
Cable Ties

B2.  
Cable  
Accessories

B3.  
Stainless  
Steel Ties

C1.  
Wiring  
Duct

C2.  
Surface  
Raceway

C3.  
Abrasion  
Protection

C4.  
Cable  
Management

D1.  
Terminals

D2.  
Power  
Connectors

D3.  
Grounding  
Connectors

E1.  
Labeling  
Systems

E2.  
Labels

E3.  
Pre-Printed  
& Write-On  
Markers

E4.  
Permanent  
Identification

E5.  
Lockout/  
Tagout  
& Safety  
Solutions


F.  
Index

## Pre-Printed Marker Cards PCM Type (continued)



PCM-1T1

| Part Number | Legend | Width |      | Length |       | Markers<br>Per<br>Card | Std.<br>Pkg.<br>Card(s) | Std.<br>Ctn.<br>Card(s) |
|-------------|--------|-------|------|--------|-------|------------------------|-------------------------|-------------------------|
|             |        | In.   | mm   | In.    | mm    |                        |                         |                         |
| PCM-1L1     | 1L1    |       |      |        |       | 25                     | 25                      | 100                     |
| thru        | thru   | 0.36  | 9.14 | 1.50   | 38.10 |                        |                         |                         |
| PCM-1L3     | 1L3    |       |      |        |       |                        | 25                      | 100                     |
| PCM-2L1     | 2L1    |       |      |        |       |                        |                         |                         |
| thru        | thru   | 0.36  | 9.14 | 1.50   | 38.10 |                        | 25                      | 100                     |
| PCM-2L3     | 2L3    |       |      |        |       |                        |                         |                         |
| PCMH-3L1    | 3L1    |       |      |        |       |                        | 25                      | 100                     |
| thru        | thru   | 0.36  | 9.14 | 1.50   | 38.10 |                        |                         |                         |
| PCMH-3L3    | 3L3    |       |      |        |       |                        | 25                      | 100                     |
| PCM-4L1     | 4L1    |       |      |        |       |                        |                         |                         |
| thru        | thru   | 0.36  | 9.14 | 1.50   | 38.10 |                        | 25                      | 100                     |
| PCM-4L3     | 4L3    |       |      |        |       |                        |                         |                         |
| PCM-1T1     | 1T1    |       |      |        |       | 25                     | 25                      | 100                     |
| thru        | thru   | 0.36  | 9.14 | 1.50   | 38.10 |                        |                         |                         |
| PCM-1T3     | 1T3    |       |      |        |       |                        | 25                      | 100                     |
| PCM-3T1     | 3T1    |       |      |        |       |                        |                         |                         |
| thru        | thru   | 0.36  | 9.14 | 1.50   | 38.10 |                        | 25                      | 100                     |
| PCM-3T3     | 3T3    |       |      |        |       |                        |                         |                         |



| Part Number | Color       | Width |      | Length |       | Markers<br>Per<br>Card | Std.<br>Pkg.<br>Card(s) | Std.<br>Ctn.<br>Card(s) |
|-------------|-------------|-------|------|--------|-------|------------------------|-------------------------|-------------------------|
|             |             | In.   | mm   | In.    | mm    |                        |                         |                         |
| PCM-BLK     | Black       | .25   | 6.35 | 1.50   | 38.10 | 36                     | 25                      | 100                     |
| PCM-BRN     | Brown       | .25   | 6.35 | 1.50   | 38.10 |                        | 25                      | 100                     |
| PCM-DBL     | Dark Blue   | .25   | 6.35 | 1.50   | 38.10 |                        | 25                      | 100                     |
| PCM-DGN     | Dark Green  | .25   | 6.35 | 1.50   | 38.10 |                        | 25                      | 100                     |
| PCM-GRY     | Gray        | .25   | 6.35 | 1.50   | 38.10 |                        | 25                      | 100                     |
| PCM-LBL     | Light Blue  | .25   | 6.35 | 1.50   | 38.10 |                        | 25                      | 100                     |
| PCM-LGN     | Light Green | .25   | 6.35 | 1.50   | 38.10 |                        | 25                      | 100                     |
| PCM-ORN     | Orange      | .25   | 6.35 | 1.50   | 38.10 |                        | 25                      | 100                     |
| PCM-PNK     | Pink        | .25   | 6.35 | 1.50   | 38.10 |                        | 25                      | 100                     |
| PCM-PUR     | Purple      | .25   | 6.35 | 1.50   | 38.10 |                        | 25                      | 100                     |
| PCM-RED     | Red         | .25   | 6.35 | 1.50   | 38.10 |                        | 25                      | 100                     |
| PCM-TAN     | Tan         | .25   | 6.35 | 1.50   | 38.10 |                        | 25                      | 100                     |
| PCM-WHT     | White       | .25   | 6.35 | 1.50   | 38.10 |                        | 25                      | 100                     |
| PCM-YEL     | Yellow      | .25   | 6.35 | 1.50   | 38.10 |                        | 25                      | 100                     |

Marker size:

Full size marker – 1.50" (38.10mm). Maximum wire O.D., .38" (9.50mm).