

Our new 2012 models have arrived!

Home > Phones & Home Office > Scanners > KV-S1020C

25ppm Simplex Color Workgroup Scanner

Model number: KV-S1020C

★★★★★ This product has not yet been rated. Be the first to WRITE A REVIEW!

[Print this](#) | [Share this](#)

25ppm Simplex Color Workgroup Scanner

Available at your favorite retailer



[enlarge](#)



Tech Specifications	Reviews	Operating Manuals	Warranty & Care Plans
Simplex / Duplex	Simplex		
Rated Speed	Binary 200 dpiUp to 26 ppmColor 200 dpiUp to 26 ppm		
ADF Size	Up to 50 sheets, 3 hard cards		
Paper Size	Min.: 1.9" x 2.8" lengthMax.: 8.5" x 100" length		
Maximum Resolution	Color and B&W: 100 to 600 dpi (1dpi step)		
Daily Duty Cycle	1,000 pages		
Color Dropout	Red, Green, and Blue Multi Color Dropout - Up to 3 colors, any color		
Warranty	1-Year Limited Advance Exchange		
Interface	High-Speed USB 2.0 Up to 480 Mbps transfer rate		
Dimensions (H x W x D)	8.6" (218 mm)" x 12.5" (317 mm)" x 7.2" (182 mm)"		
Weight	9.1 lb (4 kg)		

You may also like



High Speed Multifunction Office Machine

(1 Reviews)

Suggested Retail Price: \$419.95

KX-MB3020

[LEARN MORE](#)



24PPM 4-in-1 Monochrome Laser MFP

KX-MB2030

[LEARN MORE](#)



Need assistance with your order?



Email [click here](#)



Call

1-800-405-0652

Mon-Fri 8:00 AM - 9:00 PM EST

Sat-Sun 12:00 PM - 5:00 PM EST



Live Chat [click here](#)

Recently Viewed Products



24PPM 4-in-1 Monochrome Laser MFP

Suggested Retail Price: \$189.95

KX-MB2030

[ADD TO CART](#)



High Speed Multifunction Office Machine

★★★★★ 1 Reviews

Suggested Retail Price: \$419.95

KX-MB3020

[ADD TO CART](#)



VIERA® 50" Class ST30 Series Plasma HDTV with 3D (49.9" Diag.)

★★★★★ 15 Reviews

TC-P50ST30

[View more](#)