

R4F 4MM Hexa Socket / LC Duplex x2 Patchcord 1m


Issue

15/01/2010

Page

1/1

Dimension in mm



GENERAL

Type:	End1 R4F Socket, for 4 Multimode channels. Screw thread coupling device (to be installed with a 100 Ncm torque wrench). Plastic protective cap	End2 61754-20 type LC-PC Multimode zirconia ceramic ferrule RJ-45 latching connector system Duplex with removable brace Plastic protective cap
Cable:	MM 50/125 /2.0 mm simplex cable	
Identification:	1 Self-laminated label, RADIAL / F760 858 240 / MO nb.	

CHARACTERISTICS

(depending on cable construction)

	End 1 (R4F)	End 2 (LC)
Optical : Cable assembly Insertion Loss (@ 850 nm) acc. to IEC 61300-3-4		1.00 dB max (method 6)
Mechanical : Endurance Tensile load Vibration	500 mating cycles up to 30 N (depending on cable) Acc. To IEC 61300.2.1	500 mating cycles up to 68 N (depending on cable) 10-55Hz, 1.5 mm, 2Hr./axe
Environmental: Protection Operating temperature	IP67 (plugged) -40°C to + 85°C	Not applicable -40°C to + 85°C
2002/95/EC (RoHS)	Compliant	

CREATION N°PEN : Name: MM Date: 15/01/2010 Appr.: FP				
	Issue	Revisions	Name	Appr.

RADIAL®

101, rue P. Hoffmann
93116 ROSNY/BOIS
FRANCE
Tel : (33) 0149353535
Fax : (33) 0148546363