





## Dimensions: mm (IN)

**Mechanical Specifications:**

- Type: SPST
- Operating force: 160±50gf
- Operating temperature: -25°~+70°C
- Storage temperature: -30°~+80°C
- Travel: .010+.001 -0 (.25 +.02 -.1mm)
- Stop strength: 3Kg for 15 seconds

**Electrical Specifications:**

- Life: 100,000 cycles
- Contact resistance: 100mΩ max.
- Insulation resistance: 100MΩ min. @ 500VDC
- Dielectric Strength: 250VAC for 1 minute
- Rating: 50mA / 12VDC

**Materials:**

- Cover: stainless steel
- Contacts: silver clad phosphor bronze
- Terminals: silver clad brass
- Base: PPA, black

**Soldering Process:**

- Wave soldering temperature: 260°C max. for 5 seconds
- These switches are washable. They can only be submerged after they have been soldered and returned to normal temperature.

Tactile Switch (Thru-Hole)  
101-0165

**Mountain**  
**Switch**

Available from Mouser Electronics

[www.mouser.com](http://www.mouser.com) 1-800-346-6873

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-0165](#)