


Ring Tongue Terminal



Specifications:

Connector Type	: Ring Tongue
Termination Method	: Crimp
Stud/Tab Size	: #10
Wire Size (AWG)	: 18
Contact Material	: Copper
Insulator Material	: Uninsulated
Voltage Rating	: 600V



Part Number Table

Description	Pkg. Qty	Wire Range (AWG)	Stud Size	L	W	E	C	S	T	Thick-ness	Part Number
Non-Insulated Ring Tongue Terminals	50	12 ~ 10	6	0.68	0.28	0.54	0.29	0.143	0.135	0.04	CRS-TO-1006
	500							SPC3731			
	50		8	0.73	0.38	0.69	0.44	0.174			CRS-TO-1008
	500							SPC3732			
	50		10	0.96	0.53	0.54	0.328	0.2			CRS-TO-1010
	500							SPC3733			
	50		1/4	0.54	0.54	0.69	0.44	0.264			CRS-TO-1025
	500							SPC3734			
	50		5/16	0.54	0.54	0.69	0.44	0.328			CRS-TO-1031
	500							SPC3735			
	50		3/8	0.54	0.54	0.69	0.44	0.39			CRS-TO-1037
	500							SPC3736			

Dimensions : Inches

Ring Tongue Terminal



Description	Pkg. Qty	Wire Range (AWG)	Stud Size	L	W	E	C	S	T	Thick-ness	Part Number				
Non-Insulated Ring Tongue Terminals	100	16 ~ 14	6	0.6	0.25	0.47	0.22	0.148	0.09	0.03	CRS-TO-1406				
	1,000										SPC3727				
	100		8	0.74	0.31	0.58	0.33	0.174			CRS-TO-1408				
	1,000										SPC3728				
	100		10				CRS-TO-1410								
	1,000						SPC3729								
	100		1/4	0.89	0.47	0.65	0.4	0.265			CRS-TO-1425				
	1,000										SPC3730				
	100	22 ~ 18	2	0.6	0.25	0.48	0.23	0.088	CRS-TO-1802						
	1,000								SPC3721						
	100		4			0.47	0.22	0.118	CRS-TO-1804						
	1,000								SPC3722						
	100	22 ~ 18	6	0.6	0.25	0.47	0.22	0.144	0.07	0.03	CRS-TO-1806				
	1,000										SPC3723				
	100		8					0.74			0.31	0.58	0.33	0.174	CRS-TO-1808
	1,000														SPC3724
	100		10										0.195	CRS-TO-1810	
	1,000													SPC3725	
	100		1/4			0.88	0.47	0.65			0.4	0.265	CRS-TO-1825		
	1,000												SPC3726		
	100	26 ~ 24	0	0.32	0.14	0.24	0.11	0.06	0.03		0.02	CRS-TO-2200			
	1,000											SPC3717			
	100		2	0.31									0.09	CRS-TO-2202	
	1,000													SPC3718	
	100		4	0.45	0.2	0.35	0.21	0.116				CRS-TO-2204			
	1,000											SPC3719			
	100		6					0.143				CRS-TO-2206			
	1,000											SPC3720			

Dimensions : Inches

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.