




Dimensions (In.)

Specifications:

- Type: snap-in rectangular
- VR: 4V (max.) @ Ta= 25°C
- VF: 2.1V (typ.), 2.5V (max.) @ IF= 10mA, Ta= 25°C
- IR: 100μA @ VR=4V
- Top: -10°~+50°C
- Tstg: -10°~+70°C
- Lens: diffused
- Housing: black plastic
- Mounting hole: .46" x .21"

Ta=25°C

Mouser Stock No.	IF (mA) (max.)	P (mW) (max.)	Cd(mcd)		λP (nm) (typ.)	Δλ (nm) (typ.)	Color
			min.	typ.			
351-MP072-R	30	75	.3	.5	700	100	Red
351-MP072-Y	50	125	2	4	570	30	Yellow
351-MP072-G	50	125	1.5	3	565	30	Green

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[351-MP072-Y](#)