


- Konstantstrømlader for 1-10 NiMH/NiCd-celler
- For 500 mAh-4 Ah batterier (C/10 lading)
- Lineær
- Termosikring i transformator, termisk beskyttelse i regulator, polvendings- og kortslutningssikker
- Plugg-inn enhet
- Lysdiode indikerer lading
- Tilfredsst. medisinsk std (EN 60601)
- Utskiftbare DC plugger

- Constant current charger for 1-10 NiMH/NiCd cells
- For 500 mAh-4 Ah batteries (C/10 charging current)
- Linear
- Thermal fuse in transformer, thermal protection in regulator, protected against reversed polarity and short circuit proof
- Plug-in unit
- LED indicates charging
- Complies w. medical std (EN 60601)
- Exchangeable DC plugs



Tekniske data	Technical specifications	
Inngangsspenning:	Input voltage:	230 VAC +6/-10%, 50/60Hz
Ladespenning	Charging voltage	
• Ved tomgang:	• At no load:	Max. 24 V
• Ved 400 mA:	• At 400 mA:	Min. 12 V
Ladestrøm	Charge current	
• Innstillbar:	• Adjustable:	50-400 mA
• < 8,4 V må justeres til:	• < 8,4 V must be limited to:	250 mA
Strømtrekk fra batteri ved frakoblet nett:	Leakage current from battery when mains switched off:	< 0,1 mA
Temperaturområde:	Temperature range:	-20°C - +30°C
Isolasjonsklasse:	Insulation class:	II
Elektrisk sikkerhetsstandard:	Electrical safety standard:	EN 60065, EN 60950
EMC standarder	EMC standards	
• Emisjon:	• Emission:	EN 61000-6-3
• Immunitet:	• Immunity:	EN 61000-6-1
Utgangsterminaler	Output terminals	
• Sek. ledning med/uten plugg:	• Cord with/without plug:	Tilbehør / Accessories
Mål uten plugg (LxBxH):	Dimensions without plug (LxWxH):	100 x 51 x 63 mm
Vekt:	Weight:	450 g
* Kan på bestilling leveres med andre ladestruermer.		
* Can on request be delivered with other charge current.		

28122007