



PRODUCT NO.
SEE TABLE




mat'l. code	surface	tolerance	projection	product family
AB N05-0022 MHT	ISO1302	ISO1111	ISO1406	MOD JACK
AC M05-0067 MHT	tolerances unless otherwise specified	0.XX±0.3	mm	8 POS VERTICAL
AD N08-0239 MHT	angle	0.XX±0.15	scale 2.0	PC.B. MOD JACK ASSY
AE N09-0092 SHMM	0°±2'	0.XXX±0.05	awg no	sheet 1 of 3
AF ELX-N-010675HMM	JANET	2/22/00	69255	A4
AG ELX-N-13788HMM	M.CHENG	12/19/00	type	Product Customer Drawing
AH ELX-N-1406HMM	M.CHENG	12/19/00		
Sheet revisor	PMH	AH		
index	Sheet	1 2 3		

PRODUCT NO. ④	DIM. A	DIM. B	DIM. C	STYLE	POSITIONS LOADED	CONTACT PLATING ①	NOTES
69255-X01YLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	-
-X02YLF	1.25 /0.050	2.69 /0.106	15.62/0.615	KEYED	ALL	5u" Au + high performance lubricant	-
-X03YLF	-	-	15.62/0.615	UNKEYED	2,3,4,5,6,7	5u" Au + high performance lubricant	-
-X04YLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	-
-X05YLF	-	-	15.62/0.615	UNKEYED	ALL	1.27um /50u" GXT	-
-X06YLF	1.25 /0.050	2.69 /0.106	15.62/0.615	KEYED	ALL	1.27um /50u" GXT	-
-X07YLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 5
-X08YLF	-	-	15.62/0.615	UNKEYED	3,4,5,6	5u" Au + high performance lubricant	-
-X09YLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 6
-X10YLF	-	-	13.62/0.536	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 6




- NOTES :
- SPECIAL PACKAGING.
 - SOLDER TAIL LENGTH :
 X = 0 [3.18 ±0.51 /0 .125 ±0.020]
 X = 1 [8.13 ±0.51 /0 .320 ±0.020]
 X = 2 [5.30 ±0.51 /0 .208 ±0.020]
 X = 3 [3.70 ±0.51 /0 .145 ±0.020]
 X = 4 [4.50 ±0.51 /0 .177 ±0.020]
 [FOR X = 1 TO 2 , WIRE TRUE POSITION IS NOT APPLICABLE.]
 [PACKAGING SPEC. IS GES-14-428]
 - COLOR OF HOUSING :
 Y = NIL (BLACK HOUSING)
 Y = W (WHITE, RAL1013 HOUSING)
 Y = G (GRAY, HOUSING)
 - SPECIAL REQUIREMENT :
 SEE DETAIL C FOR P/N 69255-001B FOR FEATURE DETAILS.
 - NO PANEL STOPS ON -X09Y AND -X10Y.
 - THIS PIN NUMBERING OPPOSITE TO FCC, PART 68, SUB-PART F REQUIREMENTS
 - PART NUMBERS WITH LF IN THE END ARE LEAD FREE.
 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AN OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
 - THE HOUSING TEMPERATURE WITHSTAND EXPOSURE TO 260C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5 MM MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
 - PLATING OPTION:
 MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.



SECTION B-B

KEYWAY OPTION ON 69255-002LF & -006LF ONLY.

KEYED STYLE



DETAIL C (OPTIONAL DESIGN)

mat'l. code	surface	tolerance	projection	product family
AB	ISD1302	ISO1111	ISO1406	MOD JACK
tr.ecn nldr	date	tolerances unless otherwisespecified	title	
AC	2/18/05	0.XX±0.3	mm	8 POS VERTICAL
AD	4/8/05	0.XX±0.15	scale 2.0	PC.B. MOD JACK ASSY
AE	11/10/08	0.XXX±0.05		awg no sheet 2 of 3 size
AF	01/13/10	JANET		69255 A4
AG	01/02/13	M.CHENG		type Product Customer Drawing
AH	02/18/13	M.CHENG		
sheet index	revision			
	Sheet			



PRODUCT NO. ④	DIM. A	DIM. B	DIM. C	STYLE	POSITIONS LOADED	CONTACT PLATING ①	NOTES
69255-X01YHLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	-
-X02YHLF	1.25 /0.050	2.69 /0.106	15.62/0.615	KEYED	ALL	5u" Au + high performance lubricant	-
-X03YHLF	-	-	15.62/0.615	UNKEYED	2,3,4,5,6,7	5u" Au + high performance lubricant	-
-X04YHLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	-
-X05YHLF	-	-	15.62/0.615	UNKEYED	ALL	1.27um /50u" GXT	-
-X06YHLF	1.25 /0.050	2.69 /0.106	15.62/0.615	KEYED	ALL	1.27um /50u" GXT	-
-X07YHLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 1
-X08YHLF	-	-	15.62/0.615	UNKEYED	3,4,5,6	5u" Au + high performance lubricant	-
-X09YHLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 6
-X10YHLF	-	-	13.62/0.536	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 6

MEETS PIP PROCESS PRODUCT NO.

mat'l. code		surface	tolerance	projection	product family
ltr ecn	nodr	ISQI302	ISQI001	ISQI406	MOD JACK
AB	N05-0022	MHT	2/18/05	tolerances unless otherwise specified	
AC	M05-0067	MHT	4/8/05	0.XX±0.3	
AD	N08-0239	MHT	11/10/08	0.XX±0.15	
AE	N09-0092	SI MM	01/13/10	0.XXX±0.05	
AF	ELX-N-010675	SI MM	3/14/12	JANET	2/22/00
AG	ELX-N-13788	Henry	01/02/13	M.CHENG	12/19/00
AH	ELX-N-1406	Henry	02/18/13	M.CHENG	12/19/00
sheet index	revision				
	sheet				



8 POS VERTICAL
PC.B. MOD JACK ASSY
awg no sheet3of3 size
69255 A4
type Product Customer Drawing