






1.0mm Pitch

SERIES

6208


1.0mmピッチ ZIF ストレート DIP 片面接点 スライドロック

1.0mmPitch ZIF Vertical Through hole Single-sided contact Slide lock



基板取付寸法 (コネクタ搭載側)
MOUNTING LAYOUT
(t=1.2~1.6)

種類 KIND	公差 TOLERANCE		
	P	W	M
FPC	±0.02	±0.05	±0.05
FFC	±0.05	±0.03	±0.1



寸 法 表 DIMENSION										収納数量 UNITS/TUBE
極 数 No. of Pos	型 番 ASSEMBLY NUMBER	A	B	C	D	E	F	G		
5	0X 6208 XX0 105 XXX+	4.0	10.4	11.4	3.4	5.0	6.5	0.8	42	
6	↑ 106 ↑	5.0	11.4	12.4	↑	↑	↑	↑	38	
7	↑ 107 ↑	6.0	12.4	13.4					35	
8	↑ 108 ↑	7.0	13.4	14.4					33	
9	↑ 109 ↑	8.0	14.4	15.4					31	
10	↑ 110 ↑	9.0	15.4	16.4					29	
11	↑ 111 ↑	10.0	16.4	17.4					27	
12	↑ 112 ↑	11.0	17.4	18.4					26	
13	↑ 113 ↑	12.0	18.4	19.4					24	
14	↑ 114 ↑	13.0	19.4	20.4					23	
15	↑ 115 ↑	14.0	20.4	21.4					22	
16	↑ 116 ↑	15.0	21.4	22.4					21	
17	↑ 117 ↑	16.0	22.4	23.4					20	
18	↑ 118 ↑	17.0	23.4	24.4					19	
19	↑ 119 ↑	18.0	24.4	25.4	↓	↓	↓	↓	18	
20	↑ 120 ↑	19.0	25.4	26.4	3.4	5.0	6.5	0.8	18	
21	↑ 121 ↑	20.0	26.4	27.4	3.6	5.2	6.7	1.0	17	
22	↑ 122 ↑	21.0	27.4	28.4	↑	↑	↑	↑	17	
23	↑ 123 ↑	22.0	28.4	29.4					16	
24	↑ 124 ↑	23.0	29.4	30.4	↓	↓	↓	↓	16	
25	↑ 125 ↑	24.0	30.4	31.4	3.6	5.2	6.7	1.0	15	
26	↑ 126 ↑	25.0	31.4	32.4	3.9	5.5	7.0	1.3	15	
27	↑ 127 ↑	26.0	32.4	33.4	↑	↑	↑	↑	14	
28	↑ 128 ↑	27.0	33.4	34.4					14	
29	↓ 129 ↓	28.0	34.4	35.4	↓	↓	↓	↓	13	
30	0X 6208 XX0 130 XXX+	29.0	35.4	36.4	3.9	5.5	7.0	1.3	13	

注文コード ORDERING CODE

XX 6208 XX0 1XX XXX+

08: マガジン TUBE PACKAGE
(ONLY WITHOUT KINKED BOSS)00: トレー梱包
TRAY PACKAGE0: キンク有
WITH KINKED1: キンク無
WITHOUT KINKED

0: ボス無 WITHOUT BOSS

1: ボス付 WITH BOSS

極数
NUMBER
OF
POSITIONS

RoHS 対応品

RoHS Compliant Product

001+: スズ銅めっき Sn-Cu Plated

020+: 金めっき Au Plated


生産対応可能極数については、営業部に
ご確認願います。Feel free to contact our sales department
for available numbers of positions.

SERIES

SERIES

6208

1.0mmPitch Vertical SMT Slide lock



XX 6208 XXX 0XX XXX+

RoHS Compliant Product

852+ : 金めっき Au Plated

Feel free to contact our sales department for available numbers of positions.



1.0mm Pitch

SERIES

6208



エンボス梱包品 SMT

Tape and Reel Package SMT





SECT. E-E

型番 ASSEMBLY NUMBER	極数 NO.OF POS.	A
00 6208 505 110 XXX +	5	11.6
↑ 506 ↑	6	12.6
507	7	13.6
↑ 508 ↑	8	14.6
509 ↓	9	15.6
00 6208 510 110 XXX +	10	16.6





SECT. E-E

型番 ASSEMBLY NUMBER	極数 NO.OF POS.	A
00 6208 511 210 XXX +	11	17.6
↑ 512 ↑	12	18.6
513	13	19.6
↑ 514 ↑	14	20.6
515 ↓	15	21.6
00 6208 516 210 XXX +	16	22.6




SECT. E-E

型番 ASSEMBLY NUMBER	極数 NO.OF POS.	A
00 6208 517 310 XXX +	17	23.6
↑ 518 ↑	18	24.6
519	19	25.6
↑ 520 ↑	20	26.6
521	21	27.6
↑ 522 ↑	22	28.6
523	23	29.6
↑ 524 ↑	24	30.6
525 ↓	25	31.6
00 6208 526 310 XXX +	26	32.6



SECT. E-E



SECT. D-D

型番 ASSEMBLY NUMBER	極数 NO.OF POS.	A
00 6208 527 410 XXX +	27	33.6
↑ 528 ↑	28	34.6
529 ↓	29	35.6
00 6208 530 410 XXX +	30	36.6

注文コード ORDERING CODE

00 6208 5XX X10 XXX+

極数
NUMBER
OF
POSITIONS

RoHS 対応品

RoHS Compliant Product

バリエーション VARIATION CODE

- 1: エンボス Tape & Reel 24.0mm
- 2: エンボス Tape & Reel 32.0mm
- 3: エンボス Tape & Reel 44.0mm
- 4: エンボス Tape & Reel 56.0mm

000+: スズ銅めっき Sn-Cu Plated

009+: カーボンフレキ対応スズ銅めっき Sn-Cu Plated,C/Ag type

008+: 金めっき Au Plated

生産対応可能極数については、営業部に
ご確認願います。Feel free to contact our sales department
for available numbers of positions.

梱包数量 1000個/リール

PACKING QUANTITY: 1000/Reel