



Integrated Device Technology

The Analog and Digital Company™

[Products](#) | [Applications](#) | [Search](#) | [Support](#) | [Investor](#) | [About IDT](#)[Power Management Solutions](#) [Applications](#) [Desktop](#) [9P62000](#) [9P62000NLG](#)

9P62000NLG

[Description](#) | [Parameters](#) | [Package](#) | [Distributor Inventory](#) | [Contacts](#)

Customer Support / Technical Support

DESCRIPTION

4 PHASE PWM CONTROLLER

Generic Part:

[9P62000](#)

Category:

[Desktop](#)

PARAMETERS

Package	VFQFPN 64
Spec	VR11.1
Phase	3 - 4
Integrated Driver	Y or N or 3
Input Voltage	5V / 12V
Temperature	C

PACKAGE

Package	VFQFPN 64 (NLG64)
Description	VFQFP-N 9.0 X 9.0 X 0.9 MM - NO LEAD
Status	Active
Class	PLASTIC
Category	Green
Pb (Lead) Free	Yes
Pb Free Category	e3 Sn
Mark	NLG
Package Type	VFQFPN
Lead Count	64
Length	9.0 mm
Width	9.0 mm
Thickness	0.9 mm
Pitch	0.5 mm
Tube / Tray	TRAY
Quantity per Tube/Tray	207
Quantity per Reel	3000
Moisture Sensitivity Level (MSL)	3
Moisture Exposure Floor Life	168hrs @<30C/60% RH
Peak Reflow Temperature	260°C
Rebake Conditions	48hrs@125C
Related Package Documents	view documents

DISTRIBUTOR INVENTORY

Part	Distributor	Qty	Date	RFQ	Order
No matches found.					

CONTACTS

Sales Offices

[► Sales Offices and authorized distributors](#)

Technical Support

ASSP Computing

[► WWW: Clock Help](#)