



THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROVED
XXB-52X-D		C	ECN 9285	08/20/01	K.C.
		D	ADD NOTE & CHANGE P/N TO ROHS COMPLIANT PER ECN D831	04/21/05	M.G.



WIRE DIAGRAM

P1	OPEN END
1	GRAY
2	ORANGE
3	BLACK
4	RED
5	GREEN
6	YELLOW
7	BLUE
8	BROWN

T.B.D.	GLF-488-148-525-D	GLF-121-810-022	14.0 FT [4.3 M]	50.0 IN [1270.0 MM]	WHITE
T.B.D.	GLF-488-148-524-D	GLF-121-810-012	14.0 FT [4.3 M]	50.0 IN [1270.0 MM]	BLACK
T.B.D.	GLF-488-148-523-D	GLF-121-810-002	14.0 FT [4.3 M]	50.0 IN [1270.0 MM]	SILVER SATIN
T.B.D.	GLF-488-108-522-D	GLF-121-810-021	10.0 FT [3.0 M]	42.0 IN [1066.8 MM]	WHITE
T.B.D.	GLF-488-108-521-D	GLF-121-810-011	10.0 FT [3.0 M]	42.0 IN [1066.8 MM]	BLACK
T.B.D.	GLF-488-108-520-D	GLF-121-810-001	10.0 FT [3.0 M]	42.0 IN [1066.8 MM]	SILVER SATIN
T.B.D.	GLF-488-078-525-D	GLF-121-810-020	7.0 FT [2.1 M]	28.0 IN [711.2 MM]	WHITE
H3882-07C-ND	GLF-488-078-524-D	GLF-121-810-010	7.0 FT [2.1 M]	28.0 IN [711.2 MM]	BLACK
T.B.D.	GLF-488-078-523-D	GLF-121-810-000	7.0 FT [2.1 M]	28.0 IN [711.2 MM]	SILVER SATIN
T.B.D.	GLF-488-058-522-D	GLF-121-810-023	5.0 FT [1.5 M]	22.0 IN [558.8 MM]	WHITE
T.B.D.	GLF-488-058-521-D	GLF-121-810-013	5.0 FT [1.5 M]	22.0 IN [558.8 MM]	BLACK
T.B.D.	GLF-488-058-520-D	GLF-121-810-003	5.0 FT [1.5 M]	22.0 IN [558.8 MM]	SILVER SATIN
DIGI-KEY PART NUMBER	ID1 PART NUMBER	ID1 CABLE PART NUMBER	EXTENDED LENGTH "X"	RETRACTED LENGTH "R"	
TABULATION BLOCK					

NOTES: UNLESS OTHERWISE SPECIFIED.

1. TEST CABLE FOR ALL OPENS & SHORTS.
2. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.
3. MARK OUTSIDE OF SHIPPING BOX WITH CUSTOMER PART NUMBER.
4. PLACE BAR CODE LABEL ON THE OUTSIDE OF EACH SHIPPING BOX LABEL DETAIL SEE DWG 090-990-001.
5. ALL MATERIAL SHOULD BE ROHS COMPLIANT.

THIRD ANGLE PROJECTION		I/O INTERCONNECT	
		SANTA ANA, CALIFORNIA	
DR. BY	JOHNNY SUN	DATE	04/21/05
DR. CHECKED		TITLE	8P8C COIL CABLE TO OPEN END, CABLE ASSEMBLY P/N: H388X-XXC-ND
REV.		PART NO.	GLF-488-XXB-52X-D
DRAWN		DWG NO.	GLF-488-XXB-52X-D
CUT/PAID		CUSTOMER	DIGI-KEY
SA		SCALE	NONE
UNLESS OTHERWISE NOTED:		REV.	D
1) DIMENSIONS ARE IN INCHES (MILLIMETER)		SHEET 1 OF 1	
2) TOLERANCES:			
XXX ± 0.25 [6.35]			

ITEM	QTY	MFG.	ID1 PART NO.	DESCRIPTION
2	"X" FT	ID1	SEE "TABULATION BLOCK"	MODULAR COIL CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, PVC JACKET, (SEE TABULATION BLOCK FOR COLOR). ROHS COMPLIANT.
1	1 PC	ID1	GLF-325-881-50X	CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50u" Aw, FLAT TYPE EXIT. ROHS COMPLAINT.

CABLE ASSEMBLY PARTS LIST