


EDZ960/X



2-16 poles, Spacing 7.62 mm

insert required no. of poles **X**

How to order see page 5



*factory wiring



Ratings:

Rated Voltage

300V

400 V

Rated Current

15 A

12 A (T60)

Wire Size

AWG* 28-12

2.5 mm²

Test Voltage

6 kV/3

Rated Torque/ScrewSize

0.5 Nm/M3

Max. Rated Cross Section

Single Wire (solid)

2.5 mm²

Stranded Wire (flexible)

2.5 mm²

Stranded wire with Ferrules

2.5 mm²

Dimensions

Spacing

7.62 mm

Stripped Length

6.0 mm

Materials

Insulating Material

PA

Flammability Class

UL94 V-0

Temperature Range

-30°C/+105°C

Terminal Block



CuZn

Contact

CuSn

Color

Green



P = No. of poles