

Product data sheet

Characteristics

7S

IMIT SWITCH LEVER MS+ML +OPTIONS

Product availability : Stock - Normally stocked in distribution facility



Price* : 22.70 USD



Main

Range of product	9007
Series name	Miniature potted
Product or component type	Limit switch lever
Device short name	9007MS/ML
Associated complete product	9007ML04.. 9007MS04..
Movement of operating head	Rotary
Type of operator	Nylon spring return spring rod lever 6 in (152.40 mm) 0.3" (7.6 mm) diameter rod
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By any moving part
Net weight	0.1 lb(US) (0.05 kg)

Environment

Ambient air temperature for operation	-40...221 °F (-40...105 °C)
Ambient air temperature for storage	-40...221 °F (-40...105 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22421 - LIMIT SWITCHES,ARMS FOR 9007MS
Discount Schedule	DS1
GTIN	00785901216384
Nbr. of units in pkg.	1
Package weight(Lbs)	0.1 lb(US) (0.05 kg)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	15.24 in (38.710 cm)
Package 1 width	6.00 in (15.240 cm)
Package 1 Length	38.71 in (98.322 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP) and Diisobutyl phthalate (DINP) which is known to the State of California to cause Carcinogen and Reproductive harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Contractual warranty

Warranty	18 months
----------	-----------