


TECHNICAL SPECIFICATIONS

Material:	Zinc, Nickel Plated
Operating Temperature:	-40°C to +120°C
Cable Entry:	Top Entry
Thumbscrews:	UNC 4-40 (Standard) M2,5 or M3 on request
Cable O.D:	Up to 13mm (Size 9-37) Up to 17mm (Size 50)
Accessories:	See page 190-194
Assembly Instruction:	See page 200



Features:

- Available in sizes 9-15-25-37-50*
- Excellent EMI Shielding
- Re-openable
- Strain relief inserts ensure a secure termination
- Full Metal Jackscrew as standard.
- Also available with Metalized (RAHI) grommets
See page 28




NEW: Size 50 now available




Size MHDTZK	Dim A	Dim B	Dim C
9-way	31,0	39,5	15,0
15-way	39,5	41,5	15,0
25-way	53,5	48,5	15,0
37-way	71,0	53,0	15,0
50-way	67,5	54,0	18,7

Grommet Sizes / DTZK50:



Grommet Sizes / DTZK09-37:



Ordering information:

Size:	P/N - Kitted:	Product Code:
9-way	6560-0105-01	MHDTZK-N-09-RA-K
15-way	6560-0105-02	MHDTZK-N-15-RA-K
25-way	6560-0105-03	MHDTZK-N-25-RA-K
37-way	6560-0105-04	MHDTZK-N-37-RA-K
50-way	6560-0105-05	MHDTZK-N-50-RA-K

Size:	P/N - BULK:	Product Code:
9-way	6561-0105-01	MHDTZK-N-09-RA
15-way	6561-0105-02	MHDTZK-N-15-RA
25-way	6561-0105-03	MHDTZK-N-25-RA
37-way	6561-0105-04	MHDTZK-N-37-RA
50-way	6561-0105-05	MHDTZK-N-50-RA