






REV.	DATE	DESCRIPTION
A	02/09/06	UPDATE DRAWING FORMAT
B	05/08/07	REVISE BARREL, FERRULE DIMENSIONS, ADD CRIMP NOTES



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:
1. CRIMPED FERRULE HEX CRIMP SIZE .128"
2. CRIMPED CONTACT PIN SQ. CRIMP SIZE 0.7mm

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex					
7						DRAWN	G.R.S.	05/08/07							
6						CHECKED									
5	HEAT SHRINK TUBE			1		ISSUED				PART DESCRIPTION SMB MINI CRIMP JACK – 75ohm (FOR 179/U CABLE)					
4	FERRULE	COPPER	NICKEL	1		SHEET		1 OF 1							
3	CONTACT PIN	BRASS	GOLD	1	DO NOT SCALE DRAWING				PART NO. 142181–75						
2	INSULATOR	TEFLON	NATURAL	1											
1	BODY	BRASS	NICKEL	1											
DESCRIPTION					MATERIAL	FINISH	QTY	CAD FILE C:/142/142181–75.DWG		DWG. NO. 142181–75.DWG			REV. B	SIZE A	SCALE NA