

HUBER+SUHNER® DATA SHEET

Within Series Adapter: 32_MMBX-50-0-2/111_N

Rev.: B



Description

Adaptor plug/plug

Interface standards
SUHNER-MMBX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Weight 0.0004 kg

Environmental Data

Operating Temperature -55 °C to 155 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

Centre contact	Copper Beryllium Alloy
Outer contact	Bronze
Body	Bronze
Insulator	PFA / PTFE

Surface Plating

Gold Plating (Nickel underplated)
SUCOPRO Plating
SUCOPRO Plating

Related Documents

Outline drawing	DOU-00013784
Catalogue drawing	DCA-00013786

Ordering Information

Single package	32_MMBX-50-0-2/111_NE
Bulk 100 pcs package	32_MMBX-50-0-2/111_NH

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions