

SL-120-G-10

(2,54 mm) .100"

SL, SDL SERIES

LOW PROFILE MACHINED SOCKET STRIPS

FEATURES

- Achieve low profile without sacrificing insertion depth!
- Choice of four precision screw machined lead styles.
- Exceptionally low profile, down to (2,11 mm) .083" off of board.
- Mates with BBL or BDL for board stacking spaces down to (3,89 mm) .153"

SPECIFICATIONS

For complete specifications see www.samtec.com?SL or www.samtec.com?SDL

Insulator Material:

Black Glass Filled Polyester

Contact/Shell Materials:

BeCu/Brass

Plating:

Au or Sn over 50µ" (1,27 µm) Ni

Operating Temp Range:

-55°C to +125°C with Gold

-55°C to +105°C with Tin

Contact Resistance:

10 mΩ

Insertion Force:

(Single contact only)

Standard =

9 oz (2,50 N) avg.,
16 oz (4,45 N) max
((0,43 mm) .017" DIA probe)

Low Insertion Force =

2.5 oz (0,70 N) avg.,
5.5 oz (1,53 N) max
((0,43 mm) .017" DIA probe)

Withdrawal Force:

(Single contact only)

Standard =

2.5 oz (0,70 N) avg.,
1.5 oz (0,42 N) min
((0,43 mm) .017" DIA probe)

Low Insertion Force =

2.0 oz (0,56 N) avg.,
0.5 oz (0,14 N) min
((0,43 mm) .017" DIA probe)

RoHS Compliant: Yes

Lead-Free Solderable:

Wave only

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Note: Some lengths, styles and options are non-standard, non-returnable.

Mates with:
TS, TD, HTS, BBS, BBD,
BBL, BDL, BHS

TYPE
STRIP

1

NO. PINS
PER ROW

PLATING
OPTION


LEAD
STYLE

SL


= Single Row Low Profile Socket Strip

SDL

= Double Row Low Profile Socket Strip



01
thru
32



01
thru
36

-G

= 30µ" (0,76 µm)
Gold contact,
10µ" (0,25µm)
Gold shell

-T

= 30µ" (0,76 µm)
Gold contact,
Tin shell


-TT

= Tin contact and shell
(LIF not available)

Low Insertion Force (LIF) Available

-10


Low Profile
(Hollow Leg)



Contact Length =
(2,11 mm) .083"
Lead DIA Accepted =
(0,38 mm) .015" to (0,51 mm) .020"
Insertion Depth =
(2,67 mm) .105" to (4,32 mm) .170"
Style 10 Component Part No. =
SC-3P1

-11


Low Profile
(Standard Mount)
For LIF specify -31



Contact Length =
(1,58 mm) .062"
Lead DIA Accepted =
(0,41 mm) .016" to (0,53 mm) .021"
Insertion Depth =
(2,03 mm) .080" to (2,67 mm) .105"
Style 11 Component Part No. =
SC-4P1
Style 31 Component Part No. =
EZ-4P1

-12


Micro-Socket
(Hollow Leg)



Contact Length =
(1,58 mm) .062"
Lead DIA Accepted =
(0,41 mm) .016" to (0,51 mm) .020"
Insertion Depth =
(1,65 mm) .065" to (3,81 mm) .150"
Style 12 Component Part No. =
SC-5P1

-19

Micro-Socket
(Hollow Leg)
For LIF specify -39



Contact Length =
(1,58 mm) .062"
Lead DIA Accepted =
(0,41 mm) .016" to (0,51 mm) .020"
Insertion Depth =
(1,65 mm) .065" to (3,56 mm) .140"
Style 19 Component Part No. =
SC-8P1
Style 39 Component Part No. =
EZ-8P1

Micro
Socket

Standard
Socket

(Reference only.
Not available
with SL & SDL)

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685