

5

4

3

2





1

D

C

B

A




PCB Layout, Component side

SPECIFICATION

Filter type	C
Performance level	PL2
Capacitance	$3900\text{pf} \pm 20\%$
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	$>1\text{G}\Omega$

FREQUENCY (MHz)	ATTENUATION (dB)
5	6dB
10	11dB
50	25dB
100	35dB
500	35dB
1000	32dB

				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4
			Detail.	8-JUL-02	CV	
			Insp.	09/12/11	JB	
			Stand.			
36283	09/12/11	SD				
31589	13/01/04	AF				
31058	8-JUL-02	CV				
Mod.	Dat.	Name				

HARTING EURL
F-95972 ParisD-Sub, male, straight,
25 Poles, with turned
solder pin and hole

TB 09643227240

Sub.

Mo?Mstab/
Scale

1.5:1

Blatt/ Page

3 / 4