







SPECIFICATIONS:

- Material:
  - Body: PA66
  - Pin: Brass
- Wire range: N/A
- Electrical rating: 300V, 15A.
- Wire strip length: N/A
- Operating temperature: -40C to +105C.
- Max torque: N/A
- Insulation resistance: DC 500V, 500M.
- Dielectric withstand: AC 2500V for 1 minute.
- Breakdown voltage: 4000V.
- $A = (N \times P) + 2.0\text{mm}$
- $B = (N - 1) \times P$
- $P (\text{PITCH}) = 5.08\text{mm} (.200")$
- N = Number of positions available 2 through 24.

|                                                                                                                                    |  |  |                    |                                                      |                                       |              |                          |                                                                                                                               |                               |                      |                        |  |
|------------------------------------------------------------------------------------------------------------------------------------|--|--|--------------------|------------------------------------------------------|---------------------------------------|--------------|--------------------------|-------------------------------------------------------------------------------------------------------------------------------|-------------------------------|----------------------|------------------------|--|
| ENTER DESCRIPTION<br>EC NO: NEO2006-0310<br>DRAWN: LROTHAUS 2006/01/09<br>CHKD: CYORK 2006/01/09<br>APPR: JPAWLICK 2006/01/10<br>A |  |  | DESCRIPTION<br>REV | QUALITY SYMBOLS                                      | GENERAL TOLERANCES (UNLESS SPECIFIED) |              | DIMENSION STYLE<br>MM/IN |                                                                                                                               | SCALE<br>4:1                  | DESIGN UNITS<br>INCH | THIRD ANGLE PROJECTION |  |
|                                                                                                                                    |  |  |                    | ▽=0                                                  | mm                                    | INCH         | DRAWN BY                 | DATE                                                                                                                          | 5.08MM, EURO HEADER, VERTICAL |                      |                        |  |
|                                                                                                                                    |  |  |                    | ◇=0                                                  | 4 PLACES ± ---                        | ±.0015       | LROTHAUS                 | 12/6/05                                                                                                                       |                               |                      |                        |  |
|                                                                                                                                    |  |  |                    | 3 PLACES ±0.038                                      | ±.005                                 | CHECKED BY   | DATE                     |                                                                                                                               |                               |                      |                        |  |
|                                                                                                                                    |  |  |                    | 2 PLACES ±0.13                                       | ±.01                                  | C. YORK      | 01/06/06                 |                                                                                                                               |                               |                      |                        |  |
|                                                                                                                                    |  |  |                    | 1 PLACE ±0.3                                         | ±---                                  | APPROVED BY  | DATE                     | MOLEX MOLEX INCORPORATED                                                                                                      |                               |                      |                        |  |
|                                                                                                                                    |  |  |                    | ANGULAR ± 2 °                                        |                                       | MATERIAL NO. |                          | DOCUMENT NO.                                                                                                                  |                               | SHEET NO.            |                        |  |
|                                                                                                                                    |  |  |                    | DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS |                                       | SEE CHART    |                          | SD-39531-002                                                                                                                  |                               | 1 OF 1               |                        |  |
|                                                                                                                                    |  |  |                    |                                                      |                                       |              |                          | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |                               |                      |                        |  |

